Nuvo® P100 Player

Flexibility, meet high fidelity. Expertly engineered to deliver 40 watts of high-fidelity audio, built-in listening variety and allowing for both wired and wireless setup, the P100 player is ideal for introducing music into hard-to-wire homes or easily adding zones to an existing Player Portfolio system.

- High-fidelity audio is delivered to every area of your home, and kept perfectly in sync.
- Compatible with Legrand's other Nuvo Player Portfolio products for a truly custom, easily expandable system (up to sixteen zones).
- Supports both wired ethernet and wireless 802.11n configuration options adding flexibility for any home.
- Includes 802.11n wireless capability and utilizes both 2.4 and 5 Ghz bands, for fast signals and broad coverage.
- All your favorite music is right at your fingertips with easy access to networked computers, streaming Internet Radio, and even audio content stored on any Android or iOS device.
- Connect to storage devices, analog equipment, or home theater receivers through the unit's audio line-in, line-out, or USB ports.
- Manage your music via the convenient wall-mounted P10 keypad or wirelessly from the palm of your hand with free apps for your Apple or Android device.

Streaming services subject to geographic availability.

Nuvo® P100 Player

SPECIFICATIONS

Input/Output Connectors	
Line Input	1 - TRS 3.5 mm stereo jack
Line Output	1 - TRS 3.5 mm stereo jack
Speaker Output	4 - Gold 5-way binding post
USB 2.0 Connection (Type A)	1
Local Area Network (LAN)	1 - RJ45
Supported Audio Formats	
Music File (via USB or network)	MP3
	WMA
	AAC
	Ogg Vorbis
	FLAC
	WAV
Internet Radio:	Pandora
	Sirius/XM
	iHeart Radio
	Spotify
	TuneIn
	Deezer
	Napster
IP Control	Apple iTouch®
	Apple iPhone®
	Apple iPad®
	Android Mobile
	Android Tablet
Network Connectivity	
LAN (Wired Connection)	10/100base-t Ethernet
Wireless Connection	MIMO, 2 TX + 2 RX Channels
	IEEE 802.11a/b/g/n
	Wi-Fi Alliance CERTIFIED™
Amplifier Output	
Rated Output Power (8 ohm)	40W (20W x 2)
Two channels driven 20 Hz – 20 KHz @ 0.5% distortion	
Rated Distortion (1/2 Power)	0.20%
Speaker Impedance	6 – 8 ohms
Frequency Response (20 - 20kHz)	+/-0.5 dB
Damping Factor	50+
Signal-to-Noise Ratio at rated output	94 dB A – weighted

Line Output:	
Output Level	0-1000 mV RMS
Output Impedance	5 Ohms
Signal-to-Noise Ratio at rated output	88 dB A – weighted
Line Input:	
Input Impedance	10 KOhms
Input Overload	2.3 V RMS
Audio Processing	
Bass Equalization	+/-12 dB range
Treble Equalization	+/-12 dB range
Balance	
Regulatory Approvals	
Safety	cTUVus, CE-LVD
EMC	FCC, IC, CE-EMC, C-Tick
Environmental Compliance	RoHS
Power Requirements	
Input Voltage	100 – 240VAC, 50/60 Hz
Power Consumption (max)	70 W
Power Consumption (typical – 1/8 audio power)	13 W
Operating Temperature	0° C to 40° C
Physical Specifications	
Unit Size (mm)	43 H x 187 W x 137 D
Unit Size (inch)	1.69 H x 7.36 W x 5.39 D
Unit Weight (kg)	0.635
Unit Weight (pounds)	1.40
Shipping Specifications	
Unit Size (mm)	240 L x 230 W x 66 H
Unit Size (inch)	9.45 L x 9.06 W x 2.60 H
Unit Weight (kg)	1.25
Unit Weight (pounds)	2.75
Languages Supported	English, Spanish, French Portuguese, German, Italian

Legrand reserves the right to change specifications without notice.

designed to be better™

legrand®

Legrand, North America

3015 Kustom Drive
Hebron, KY 41048
United States
844.334.8044
www.legrand.us/nvuo