legrand®

Pass & Seymour

Weatherproof Boxes & Covers
While-In-Use Covers
Single, Shallow, Deep & Two Gang

WIUC10-L, WIUC10-S, WIUC10-DL, WIUC20-L

Innovative design in addition to the latest NEC requirements provides weather protection while-in-use.



Corner hinges allow versatile polycarbonate covers to be installed either vertically or horizontally. They provide generous interior room to accommodate bends in even the heaviest cords. They are lockable to prevent tampering, and deliver excellent weather resistance thanks to neoprene-blend gasketing, a cord flap seal and our exclusive WaterShed™ channel.

Features & Benefits

Exclusive cord flap gasket inhibits water splash from driving rain or sprinklers.

Sturdy polycarbonate construction resists impacts and harsh weather.

Patented corner hinge and cord opening allow vertical or horizontal installation.

Exclusive WaterShed™ Channel keeps water moving outside while cord flap keeps the inside dry.

Preapplied gasket easier to install, saves time, won't get lost or damaged.



WIUC10-SC

Paintable, textured finish hides scratches.

Patented trigger latch opens easily with one finger, yet is lockable to prevent tampering.

Sturdy, molded-in hinge withstands hard use.

Installs without removing electrical device, thanks to patented, keyed mounting holes.

Roomy interior provides space for plugs and cord bends.

Shallow profile models have 1" shorter top lid than prior models.

The 2002 NEC Section 406.8(B)(1) requires that all 15 and 20 Amp, 125 and 250 Volt outdoor receptacles in wet locations have a cover that is weatherproof — even when a plug is inserted into the receptacle.

Field Uses/Vertical Markets

- Industrial
- Retail
- Health Care
- Office
- Education
- Hospitality/Lodging
- Institutional
- Multiple Dwelling

legrand®
Pass & Seymour

Weatherproof Boxes & Covers
While-In-Use Covers
Single, Shallow, Deep & Two Gang

Ordering Information

Catalog Number	Bottom Color	Top Color	Device Plates Provided	Plate Width
Single Gang				
WIUC10-GL **WIUC10-CL** **WIUC10-WL**	Gray Gray White	Gray Clear White		2⅜"
Single Gang Shallow				
WIUC10-SG **WIUC10-SC** **WIUC10-SW** **WIUC10-SB**	Gray Gray White White	Gray Clear White Clear		2⅜"
Single Gang Deep				
WIUC10-DGL **WIUC10-DCL** **WIUC10-DWL**	Gray Gray White	Gray Clear White		2⅜"
Two Gang				
WIUC20-GL **WIUC20-CL** **WIUC20-WL**	Gray Gray White	Gray Clear White		2"
Extra Plate Kits				
WIU10-PK **WIU10-PKW**	Gray White		Single Gang Plate Kit	2⅜"
WIU20-PK **WIU20-PKW**	Gray White		Two Gang Plate Kit 	2"

Snap-in device plates require no tools to install and won't fall out. See chart for plates provided with each catalog number.

For more information on these and other P&S products refer to our Product Guide or visit our web site.

Weatherproof Boxes & Covers
While-In-Use Covers
Single, Shallow, Deep & Two Gang

legrand®
Pass & Seymour

Technical Specifications

3rd Party Compliance

cULus Listed.
Covers conform to NEMA 3R.
Complies with 2002 NEC Section 406.8(B)(1).

Performance

Environmental	Weatherproof

Materials

Body	Polycarbonate
Cover	.125" Polycarbonate
Cover Finish	Textured
Screws	302 Stainless Steel
Gasket	Closed Cell Foam, Neoprene Blend
Insert Plate	Polycarbonate

Warranty

1 Year

SINGLE GANG, SINGLE GANG SHALLOW, SINGLE GANG DEEP COVERS



SINGLE GANG COVER



SINGLE GANG SHALLOW COVER



SINGLE GANG DEEP COVER



TWO GANG COVER





Complimentary Devices & Accessories

WEATHERPROOF BOXES & COVERS

- Heavy Cast Aluminum Covers
- Cast Covers
- Boxes

WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers



SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle

STRAIGHT BLADE RECEPTACLES

- Plug Tail™
- Extra Heavy-Duty
- Heavy-Duty
- Construction Grade
- Construction Grade Leaded
- Commercial Grade

GFCIs

- Specification Grade
- Hospital Grade
- Dead Front

Also available...

- Light Almond Devices
- Decorator Devices
- Hospital Grade Devices
- PlugTail™ Devices
- TVSS & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions

legrand®

Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca

SF2301R2 — Updated April 2005 — For latest specs visit www.legrand.us/passandseymour

© 2010, Legrand/Pass & Seymour GG/DG