legrand®

Pass & Seymour

# Hospital Grade Devices
# Heavy-Duty Decorator Receptacles
# IG 15 & 20A, 125V

## IG26262-HG, IG26362-HG

### *Sleek style, backed by rugged construction.*

It is easy to clean the smooth, tough nylon faces on these isolated ground receptacles. And the receptacles are easy to install, too. They feature tri-drive terminal and mounting screws, auto-ground and the exclusive P&S screw-pressure-plate back wiring system (which also supports side wiring). A sturdy, corrosion-resistant strap locks into the receptacle body for added strength.



## Features & Benefits



**IG symbol and molded-in "Isolated Ground" markings** for fast I.D. and circuit delineation.

**Nylon strap on top** eliminates potential contact with isolated ground.

**.032 inch thick, brass, triple-wipe power contacts** for lasting retention.

**Easily accessed break-off, line-contact connecting tab** for fast, easy split-circuit wiring.

**Two drive screws anchor strap** to back body and face where abrupt removal torque is strongest.

**Tri-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability.** Two back wire holes for more wiring flexibility.

**Corrosion-resistant, plated steel strap** locked in to face and back body to resist pulling away from face/body assembly.

**Auto-ground** eliminates the necessity to terminate grounding conductor to device.

IG26362-HG

## Field Uses/Vertical Markets

- Health Care
- Education
- Institutional

legrand®
Pass & Seymour

# Hospital Grade Devices
# Heavy-Duty Decorator Receptacles
## IG 15 & 20A, 125V

## Ordering Information

| Catalog Number | Rating A. | V. | Color | NEMA Config. No. |
|---|---|---|---|---|
| **Hospital Ground Isolated Ground Duplex Receptacles** Back & Side Wire | | | | |
| **IG26262-HG** | 15 | 125 | Orange | 5-15R |
| **IG26262-HGRED** | 15 | 125 | Red | 5-15R |
| **IG26362-HGW** | 20 | 125 | White | 5-20R |
| **IG26362-HG** | 20 | 125 | Orange | 5-20R |
| **IG26362-HGRED** | 20 | 125 | Red | 5-20R |

NEMA 5-15R

NEMA 5-20R

For more information on these and other P&S products refer to our Product Guide or visit our web site.

# Hospital Grade Devices
# Heavy-Duty Decorator Receptacles
## IG 15 & 20A, 125V

legrand®
Pass & Seymour

## Technical Specifications

### 3rd Party Compliance

UL Listed, File Number E140596, Standard UL498.
Federal Specification WC596, Hospital Grade.
CSA/CUL approved, File Number LR16063, Standard CSA-C22.2 No. 42.




**Dimensions for 15 & 20 Amp**

### Performance

| | |
|---|---|
| **Electrical** | |
| Dielectric Voltage | Withstands 2000V minimum |
| Maximum Working Voltage | 250V |
| Current Interrupting | Certified for current interrupting at full-rated current |
| Temperature Rise | Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current |
| **Mechanical** | |
| Terminal Identification | Terminal Identification in accordance with UL498 (Brass, White, Green) |
| Terminal Accommodation | #14 AWG – #10 AWG copper conductor only |
| Product Identification | Ratings are a permanent part of the device |
| **Environmental** | |
| Flammability | UL94 V2 |
| Operating Temperature | Maximum continuous +60°C, minimum -40°C (without impact) |

### Materials

| | | | |
|---|---|---|---|
| Face | Nylon | Terminal Screws | #8 Tri-Drive Steel (Neutral = Nickel-Plated Steel) |
| Back Body | PVC | | |
| Line Contacts | .032 688 Brass | | |
| Mounting Strap | .042 Zinc-Plated Steel | Ground Screw | #8 Hex Tri-Drive Steel |
| Ground Contacts | .040 260 Brass | Assembly Drive Screw | Zinc-Plated Steel |
| Pressure Plate | .080 Steel | Auto-Ground Clip | Stainless Steel |
| | | Mounting Screws | Tri-Drive Steel |

### Warranty

1 Year

## Complementary Devices & Accessories

### HOSPITAL GRADE DEVICES

- Receptacles, Tamper-Resistant, Decorator
- GFCIs
- TVSS
- Isolated Ground
- Plugs & Connectors

### DECORATOR DEVICES

- Construction Grade Switches
- Construction Grade Illuminated & Pilot Lighted Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Construction Grade Hallway Lights

### TVSS & ISOLATED GROUND DEVICES

- Construction Grade Isolated Ground
- Heavy-Duty Turnlok® Isolated Ground
- Heavy-Duty Isolated Ground TVSS
- Heavy-Duty TVSS
- Construction Grade TVSS

### STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Construction Grade
- Commercial Grade



### SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



### GFCIs

- Construction Grade with Auto-Ground
- Construction Grade
- Construction Grade Dead Front

## Also available...

- Light Almond Devices
- PlugTail™ Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- Wall Plates
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions

legrand®

**Legrand/Pass & Seymour**
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

**North America Headquarters**
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

**Legrand Canada**
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca

**SF713R1 — Updated January 2004 — For latest specs visit www.legrand.us/passandseymour**

© 2011, Legrand/Pass & Seymour GG/DG