legrand®

Pass & Seymour

Wall Plates
TradeMaster® Thermoplastic Nylon
One & Two Gang

TP1, TP2, TP8, TP82, TP26, TP262, TP13, TP23, TP7, TP720

Maximum durability in plastic wall plates.

Self-extinguishing nylon construction makes these TradeMaster® wall plates virtually unbreakable. They will not crack if excessive torque is applied to installation screws. They are 3/16" higher and wider than typical plastic wall plates — not enough to be apparent to the eye, but the extra size cuts costs by reducing dry wall rework.

Features & Benefits

An extra 3/16" width and height than standard size wall plates for more tolerance in covering ragged sheet rock openings.

Molded of rugged, virtually unbreakable self-extinguishing .070 inch thick thermoplastic Nylon 6.



Pre-installed mounting screws on single gang toggle, duplex receptacle and decorator openings.

Aesthetically pleasing contour design.

TP26-W, TP2-I, TP8-LA

Field Uses/Vertical Markets

- Health Care
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling

legrand®
Pass & Seymour

Wall Plates
TradeMaster® Thermoplastic Nylon
One & Two Gang

Ordering Information

Description	Catalog Number	Color
TradeMaster Toggle Switch Openings		
One Gang	TP1-I	Ivory
	TP1-W	White
	TP1	Brown
	TP1-GRY	Gray
	TP1-BK	Black
	TP1-RED	Red
	TP1-LA	Light Almond
Two Gang	TP2-I	Ivory
	TP2-W	White
	TP2	Brown
	TP2-GRY	Gray
	TP2-BK	Black
	TP2-RED	Red
	TP2-LA	Light Almond
TradeMaster Duplex Receptacle Openings		
One Gang	TP8-I	Ivory
	TP8-W	White
	TP8	Brown
	TP8-GRY	Gray
	TP8-BK	Black
	TP8-RED	Red
	TP8-LA	Light Almond
	TP8-BL	Blue
	TP8-OR	Orange
Two Gang	TP82-I	Ivory
	TP82-W	White
	TP82	Brown
	TP82-GRY	Gray
	TP82-BK	Black
	TP82-RED	Red
	TP82-LA	Light Almond
	TP82-OR	Orange
TradeMaster Decorator Openings		
One Gang 	TP26-I	Ivory
	TP26-W	White
	TP26	Brown
	TP26-GRY	Gray
	TP26-BK	Black
	TP26-RED	Red
	TP26-LA	Light Almond
	TP26-BL	Blue
	TP26-OR	Orange
Two Gang	TP262-I	Ivory
	TP262-W	White
	TP262	Brown
	TP262-GRY	Gray
	TP262-BK	Black
	TP262-RED	Red
	TP262-LA	Light Almond
	TP262-BL	Blue
	TP262-OR	Orange

Description	Catalog Number	Color
TradeMaster Blank Plates — Box Mounted		
One Gang 	TP13-I	Ivory
	TP13-W	White
	TP13	Brown
	TP13-GRY	Gray
	TP13-BK	Black
	TP13-RED	Red
	TP13-LA	Light Almond
Two Gang 	TP23-I	Ivory
	TP23-W	White
	TP23	Brown
	TP23-GRY	Gray
	TP23-BK	Black
	TP23-LA	Light Almond
TradeMaster Single Receptacle Openings		
One Gang	TP7-I	Ivory
	TP7-W	White
	TP7	Brown
	TP7-GRY	Gray
	TP7-BK	Black
	TP7-RED	Red
	TP7-LA	Light Almond
TradeMaster Power Outlet Receptacle Openings		
One Gang	TP720-I	Ivory
	TP720-W	White
	TP720	Brown
	TP720-GRY	Gray
	TP720-LA	Light Almond

For more information on these and other P&S products refer to our Product Guide or visit our web site.

Wall Plates
TradeMaster® Thermoplastic Nylon
One & Two Gang

legrand®
Pass & Seymour

Technical Specifications

3rd Party Compliance

UL Listed, Standard UL514, Cover Plates for Flush Mounted Wiring Devices.
CSA Certified.

Performance

Environmental	Chemical-Resistant
Flammability	UL94 V2

Materials

Plate Material	.070” Nylon 6
Plate Finish	Matte
Screws	Steel, Heads Painted to Match Plate Color

Warranty

1 Year



Dimensions for TradeMaster One Gang



Dimensions for TradeMaster Two Gang

Complementary Devices & Accessories

WALL PLATES

- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers



WEATHERPROOF BOXES & COVERS

- While-In-Use Covers
- Heavy Cast Aluminum Covers
- Cast Covers
- Boxes



SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Construction Grade
- Commercial Grade



GFCIs

- Construction Grade with Auto-Ground
- Construction Grade
- Construction Grade Dead Front

Also available...

- Light Almond Devices
- Decorator Devices
- Hospital Grade Devices
- PlugTail™ Devices
- TVSS & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions

legrand®

Legrand/Pass & Seymour
P.O. Box 4822
Syracuse, NY 13221-4822
800-223-4185

North America Headquarters
60 Woodlawn Street
West Hartford, CT 06110
Phone: 1.877.BY.LEGRAND (295.3472)
Fax: 1.860.232.2062
www.legrand.us

Legrand Canada
570 Applewood Crescent
Vaughan, ON, L4K 4B4
Phone: 905.738.9195
Fax: 905.738.9721
www.legrand.ca

SF2501R1 — Updated January 2004 — For latest specs visit www.legrand.us/passandseymour

© 2011, Legrand/Pass & Seymour GG/DG