




TR5362W

Tamper-resistance in a construction grade receptacle – now with Federal Specification listing!

TR5262, TR5362

Tamper-resistant child safety receptacles that conform to 2008 NEC Article 406.11 are now available in construction grade. They offer a UL Federal Specification WC596 listing at an exceptional value. The sturdy mechanical shutter system helps prevent children from inserting foreign objects into the receptacle. Corrosion-resistant plated steel straps, rugged nylon faces, and triple-wipe power contacts combine with tamper-resistant shutters to deliver safe and reliable long-term performance. Screw-pressure-plate back wiring ensures excellent electrical connections and easy installation.

Features & Benefits



3rd Party Compliance



UL Listed, File Number E140596, Standard UL498, Federal Specification WC596,
CSA/CUL Approved, Standard CSA-C22.2 No. 42. Conforms to NEMA WD-1 and WD-6.

Technical Specifications

Performance

Electrical

Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	125V
Maximum Continuous Current	TR5262 = 15A TR5362 = 20A
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current

Mechanical


Terminal Accommodation	#14 - #10 AWG copper conductor only
Product Identification	Amperage, Voltage, 3rd Party Compliance

Environmental

Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact

Materials

Face	Nylon
Back Body	PVC
Line Contacts	.032 Olin 688 Brass
Mounting Strap	.042 Zinc-Plated Steel
Ground Contacts	.040 Olin 688 Brass
Pressure Plate	.080 Steel
Tamper-Resistant Shutters	Thermoplastic
Terminal Screws	#8 Tri-Drive Brass (Neutral = Nickel-Plated Steel)
Ground Screw	#8 Hex Tri-Drive Steel; Zinc Coating with Green Chromate
Assembly Drive Screw	Zinc-Plated Steel
Auto-Ground Clip	Stainless Steel
Mounting Screws	Tri-Drive Steel



**Dimensions for
15 & 20 Amp**

Warranty

1 Year

Ordering Information

Catalog Number	Ratings		Color	NEMA Config.
	A	V		
Duplex Receptacles - Back & Side Wire				
TR5262I	15	125	Ivory	5-15R
TR5262W	15	125	White	5-15R
TR5262	15	125	Brown	5-15R
TR5262GRY	15	125	Gray	5-15R
TR5262BK	15	125	Black	5-15R
TR5262RED	15	125	Red	5-15R
TR5262LA	15	125	Light Almond	5-15R
TR5362I	20	125	Ivory	5-20R
TR5362W	20	125	White	5-20R
TR5362	20	125	Brown	5-20R
TR5362GRY	20	125	Gray	5-20R
TR5362BK	20	125	Black	5-20R
TR5362RED	20	125	Red	5-20R
TR5362LA	20	125	Light Almond	5-20R
TR5362BL	20	125	Blue	5-20R



NEMA
5-15R



NEMA
5-20R

Also available

- USB Charging Devices
- Hospital Grade Devices
- SPD & Isolated Ground Devices
- PlugTail® Wiring Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us
905.738.9195
www.legrand.ca

