PASS & SEYMOUR®

USB CHARGER DEVICES

MOBILE. READY.



CHARGE MULTIPLE MOBILE DEVICES FROM ONE USB RECEPTACLE — **WITHOUT AN ADAPTER.**

designed to be better.™

legrand®

CHARGE MORE DEVICES WITH LESS CLUTTER.

Legrand offers a full line of Pass & Seymour® charging solutions designed to power up mobile devices quickly and reliably — without the need for bulky AC adapters.
From USB-only receptacles to USB/receptacle/switch combos, these 4.2-, 3.1- and 2.1-amp devices:

- Charge multiple USB-powered devices at the same time
- Allow users to plug USB cable directly in wall without AC adapter
- Accept standard Pass & Seymour Wall Plates
- Include back and side wiring terminals for installation flexibility
- Are available in all Pass & Seymour Decorator-style colors
- Are compatible with USB 2.0 and 3.0 devices

DEVICE COMPATIBILITY

- iPad
- iPhone
- iPod
- Tablets
- Smartphones
- Handheld Video Game Systems
- Bluetooth Headsets
- Digital Cameras
- e-Readers
- GPS
- Much more

TM8USBWCC6

USB Charger with Tamper-Resistant Receptacle

Two USB "A" style charging outlets plus a 15-amp tamper-resistant receptacle

Charge two tablets simultaneously while still using receptacle

Total charging capacity of 2.1 amps

Available in Residential, Fed Spec Grade and Hospital Grade models

TM826USBWCC6

USB Charger with Duplex Decorator Tamper-Resistant Receptacle

Two USB "A" style charging outlets plus a duplex 15-amp tamper-resistant receptacle

Charge two tablets simultaneously while still using receptacles

Total charging capacity of 3.1 amps

Available in Residential, Fed Spec Grade and Hospital Grade models

TM8USB4WCC6

Quad USB Charger

Four USB ports

Can charge four tablets simultaneously

Total charging capacity of 4.2A

TM83USBWCC6

USB Charger with Single Pole/3-Way Switch

Flexible wiring allows switch to control light load or USB outlets

Convenient operation — combines ON/OFF Decorator-style switch with two separate USB ports for charging

IDEAL FOR RESIDENTIAL, COMMERCIAL, AND HEALTH CARE APPLICATIONS, INCLUDING:

- Kitchens
- Bedrooms
- Home Offices
- Airport Lounges
- College Dorms
- Hotels/Hospitality
- Common Study Areas
- Open Work Spaces
- Meeting Rooms
- Office Cubicles
- Patient Rooms
- Nurses' Stations
- Labs
- Desk Areas

TR5361USBW

TR8300HUSBW

PART NO.	DESCRIPTION	RATINGS A.	RATINGS V.	COLORS	VDC	Charging Capacity (A)
TM8USB*CC6	2 USB Chargers and Tamper-Resistant Receptacle	15	125	BK, I, LA, NI, TI, W	5	2.1
TM88USB*	2 USB Chargers and Single Tamper-Resistant Receptacle	15	125	BK, I, LA, NI, W	5	3.1
TR5261USB*	**Fed Spec Grade** — 2 USB Chargers and Tamper-Resistant Receptacle	15	125	BK, I, LA, NI, W, RED, GN, –, GRY	5	2.1
TR5361USB*		20	125			
TR8201USB*	**Hospital Grade** — 2 USB Chargers and Tamper-Resistant Receptacle	15	125	BK, I, LA, NI, W, RED, –, GRY	5	2.1
TR8301USB*		20	125			
TM83USB*CC6	2 USB Chargers with Single Pole/3-Way Switch	15	120	BK, I, LA, NI, W	5	2.1
TM8USB4*CC6	Quad USB Charger			BK, I, LA, NI, W	5	4.2
TM826USB*CC6	2 USB Chargers and Duplex Decorator Tamper-Resistant Receptacle	15	125	BK, I, LA, NI, W	5	3.1
TR5262USB*	**Fed Spec Grade** — 2 USB Chargers and Duplex Tamper-Resistant Receptacle	15	125	BK, I, LA, NI, W, RED, GN, –, GRY	5	3.1
TR5362USB*		20	125			
TR8200HUSB*	**Hospital Grade** — 2 USB Chargers and Duplex Tamper-Resistant Receptacle	15	125	BK, I, LA, NI, W, RED, –, GRY	5	3.1
TR8300HUSB*		20	125			

c UL us

*COLOR DESIGNATION

BK	Black	**RED**	Red
I	Ivory	**GN**	Green
LA	Light Almond	**–**	Brown
NI	Nickel	**GRY**	Gray
W	White		

designed to be better.™

©2013 Legrand BR1817
All Rights Reserved 10113 EMA/CGXTP

For additional technical or application-specific information, call 800-223-4185 or visit our website at www.legrand.us/PassandSeymour. We're eager to put our expertise to work for you.

Electrical Wiring Systems

P.O. Box 4822
Syracuse, NY 13221-4822
800.776.4035
www.legrand.us/PassandSeymour

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

FOLLOW US