# NUVO

## P5200 Professional Series Player

Designed exclusively for integrators, the P5200 Professional Series Player is purpose-built for custom audio installations. This premium Player provides 100 watts of power per channel at 8 ohms or 200 watts of power per channel at 4 ohms. The P5200 provides powerful sound to three listening zones with an energy efficient 2U rack-mounted design. It offers built-in access to endless music options including the most popular streaming music services and networked music collections.

- **Built-in access to streaming services, including Spotify, Pandora, iHeartRadio, TuneIn, Napster, Deezer, and SiriusXM or personal music collections on networked devices**
- **Convenient control options including the intuitive Player app, optional in-wall keypad and touch screen, or with Amazon Alexa**
- **Delivers powerful, high-fidelity audio to three independent zones with 100 watts of power per channel at 8 ohms or 200 watts of power per channel at 4 ohms**
- **Side-mounted heat sinks with no fans support the space and energy efficient 2U rack design**
- **Compatible with Legrand's other Nuvo Players for a truly custom, flexible home audio solution**
- **Connect to storage devices, analog equipment or home theater receivers through the units' analog audio line-in, line-out, or USB ports**
- **Seamless integration into advanced automation systems from Vantage, Crestron, Control4, KNX, and more - visit the Player Portfolio third party drivers page (link on product page)**
- **Remote network and device management with Domotz PRO (link on product page)**
- **Two-year warranty**

The P5200 can be hard-wired with other Players for centralized integration and system scalability. Offering quick installation, easy setup, convenient control options, and simplified integration with leading automation systems, Nuvo makes it easy to fill any space with uncompromising sound.

**Also available**

**P5050 Professional Series Player**
25W per channel at 8 Ohms

**P5100 Professional Series Player**
50W per channel at 8 Ohms

# P5200 Professional Series Player

**Input/Output Connectors**

| | |
|---|---|
| Line Input | (3) TRS 3.5 mm stereo jack |
| Line Output | (3) TRS 3.5 mm stereo jack |
| Speaker Output | (3) (Four-contact) Pluggable |
| USB 2.0 Connection | Three (3) |
| Local Area Network (LAN) | (1) RJ45 |

**Supported Audio Formats**

| | |
|---|---|
| Music File | MP3 (.mp3) |
| (USB or over network) | WMA (.wma) |
| | AAC (.acc) |
| | Ogg Vorbis (.ogg) |
| | FLAC (.flac) |
| | WAV (.wav) |

**Streaming Music Services**

Amazon Music
Deezer
iHeart Radio
Napster
Pandora
SiriusXM
Spotify
TuneIn

**Playlist Support**

WPL
M3U
PLS
iTunes

**IP Control**

Apple iTouch®
Apple iPhone®
Apple iPad®
Android Mobile
Android Tablet
Various Third-Party Systems

**Network Connectivity**

LAN (Wired Connection) 10/100Base-T Ethernet
Internal Ethernet switch to 3 independent zone nodes

**Amplifier Output (typical of three zones)**

Rated Output Power (1KHz/1% Distortion)

| | |
|---|---|
| 4 Ohm | 400 W (200 W x 2) |
| 6 Ohm | 300 W (150 W x 2) |
| 8 Ohm | 200 W (100 W x 2) |

**Total Harmonic Distortion (1/2 Power)**

| | |
|---|---|
| 100 Hz | 0.005% |
| 1 KHz | 0.005% |
| 6.67 KHz | 0.020% |

| | |
|---|---|
| **Speaker Impedance** | 4-8 Ohms |
| **Frequency Response (20Hz - 20kHz)** | +/-0.5 dB |
| **Damping Factor** | 80+ |
| **Signal-to-Noise Ratio, Rated Output** | 100 dBA |

**Line Output (Digital)**

| | |
|---|---|
| Sample Rates | 44.1kHZ - 192kHz |
| Bit Rate | 24 B |
| Signal-to-Noise Ratio, Rated Output | 120 dBA |
| THD+n | <0.0005% |
| Frequency Response (20Hz - 20kHz) | +/-0.1 dB |

**Line Input (Digital)**

| | |
|---|---|
| Sample Rates | 44.1kHZ - 192kHz |
| Bit Rate | 24 B |
| Signal-to-Noise Ratio, Rated Output | 120 dBA |
| THD+n | <0.0005% |
| Frequency Response (20Hz - 20kHz) | +/-0.1 dB |

**Line Output (Analog)**

| | |
|---|---|
| Output Level | 0-2.0 V RMS |
| Output Impedance | 470 Ohms |
| Signal-to-Noise Ratio, Rated Output | >100 dB SNR |
| THD+n | <0.005% |
| Frequency Response (20Hz - 20kHz) | +/-0.5 dB |

**Line Input (Analog)**

| | |
|---|---|
| Input Impedance | 10 kOhms |
| Input Overload | 2.0 V RMS |

**Audio Processing**

| | |
|---|---|
| Bass Equalization | +/- 12 dB range |
| Treble Equalization | +/- 12 dB range |

**Regulatory Approvals**

| | |
|---|---|
| Safety | cTUVus, CE-LVD |
| EMC | FCC, IC, CE-EMC, C-Tick |
| Environmental | RoHS |

**Power Requirements**

| | |
|---|---|
| Input Voltage | 100-240 VAC, 50/60 Hz |
| Power Consumption (max) | 1577 W |
| Power Consumption (typical - 1/8 audio power) | 171 W |
| Operating Temperature | "32° F to 104° F<br>0° C to 40° C" |

**Physical Specifications**

| | |
|---|---|
| Unit Size (mm) | 258 D x 430 W x 88 H |
| Unit Size (inch) | 10.16 D x 16.93 W x 3.46 H |
| Unit Size with feet (mm) | 258 D x 430 W x 98 H |
| Unit Size with feet (inch) | 10.16 D x 16.93 W x 3.74 H |
| Unit Weight (kg) | 5.1 |
| Unit Weight (pounds) | 11.3 |

**Shipping Specifications**

| | |
|---|---|
| Unit Size (mm) | 565 D x 330 W x 175 H |
| Unit Size (inch) | 22.24 D x 12.99 W x 6.89 H |
| Unit Weight (kg) | 5.88 |
| Unit Weight (pounds) | 12.98 |

**Languages Supported**

English, French, German,
Italian, Portuguese, Spanish

Nuvo reserves the right to change specifications without notice.



**Legrand, North America**

3015 Kustom Drive
Hebron, KY 41048
United States
844.334.8044
www.legrand.us/nuvo