NUVO

In-Wall Dual Passive 8" Subwoofer

Delivering a stand-out bass response, the In-Wall Dual Passive 8" Subwoofer brings a whole new dimension of detailed clarity to movies and music. With a discrete design that allows for space-saving in-wall placement, the NV-SUBIWDUAL8 adds a powerful low-frequency impact to medium and larger home theater or audio installations. Its sealed cabinet is constructed of durable MDF for a distortion-free, superior bass experience. A rectangular magnetic grill is included.

- **Discrete wall-mounted passive dual 8" subwoofer ideal for medium and larger sized audio installations**
- **Installation-friendly sealed cabinet design**
- **Pair up with optional NV-SUBAMP500-xx amplifier**
- **Rectangular magnetic grill included**
- **Up to two dual subwoofers may be used with optional NV-SUBAMP500-xx amplifier**
- **Lifetime warranty**
- **Space-saving design**

The NV-SUBAMP500 optional matching amplifier offers maximum versatility with rack-mount capability. The pair are designed to integrate with almost any audio system. The NV-SUBAMP500-xx features DSP (digital signal processing) for a variety of listening modes, an easy to navigate front screen for set up and use, signal-sensing power activation (optional setting) to automatically turn on the subwoofer when it detects a signal from the receiver. It will return to standby automatically after approximately 15 minutes of no signal. Unfiltered LFE / RCA stereo inputs let you easily connect the amplifier to most modern receivers. The variable crossover and phase controls allow you to match the Subwoofer output with the main speakers for premium performance and sound. Convenient 12V DC trigger inputs and outputs allow the amplifier to be controlled by external devices or control other external items. An IR input allows for simple external control as well. A three-position EQ menu setting allows the amplifier output to be tailored to any Nuvo in-ceiling or in-wall passive subwoofers. One or two NV-SUBIWDUAL8 subwoofers may be used with one NV-SUBAMP500-xx.

NV-SUBAMP500

Nuvo In-Wall Dual Passive 8" Subwoofer

Material
MDF Enclosure with Aluminum Frame and Steel Grill

Color
Black with White Grill

Unit Size

(mm)	547.6 x 347.6 x 106.8
(in)	21.6 x 13.7 x 4.2

Unit Weight

(kg)	10.2
(lbs)	22.49

Shipping

Package Dimensions (mm)	655 x 465 x 260
Package Dimensions (in)	25.8 x 18.3 x 10.2
Package Shipping Weight (kg)	12.5
Package Shipping Weight (lbs)	27.56

Humidity
70% non-condensing

Interoperability
Use up to two units with NV-SUBAMP500-xx

Mounting

In-Wall Rectangular Cutout	510mm x 310mm (19.75" x 12")

High Level Input Connector
Gold Plated Spring Loaded Binding Posts

Speaker Size
Dual 8" (200mm) High-Output

Enclosure Type
Sealed

Sensitivity
85dB

Frequency
29-200Hz

Speaker Impedance
8 Ohm

Power Consumption
250W RMS
500W Peak

Regulatory Approvals
RoHS (Restriction of Hazardous Substances Directive 2002/95/EC

Legrand reserves the right to change specifications without notice.

designed to be better™

legrand® | AV

Legrand, North America

3015 Kustom Drive
Hebron, KY 41048
United States
844.334.8044
www.legrand.us/nuvo