DATA SHEET

Infinium M4 HDFP Adapter Panel, 8 Keyed Front Non Keyed Rear LC Duplex Adapters, 16 Fiber



Overview

The Keyed 16-fiber HDFP Adapter Panels are designed to be used with the Infinium Fiber Enclosure to support LC Duplex adapters. This adapter panel has an M4 Footprint with 8 LC Duplex adapters and is equipped with plunger and grommet fasteners to hold the panels securely in place and support efficient installations. Keyed connectivity solutions offer users security and network segregation to match cords to the proper channels during installation.

Features

- **Compact high-density design:** Optimized space utilization
- **Front loading:** Easy access to connections
- **Fiber port labeling:** Provides fiber port identification for easier administration
- **Engineered polymer adapter panel:** Rugged, cost-effective design
- **Uses plunger/grommet fastener:** Holds adapter panels securely in place

Part Number	Description
HDFP-LCD16YC-A	Infinium M4 HDFP Adapter Panel, 8 Keyed Front Non-Keyed Rear LC Duplex Adapters, 16 Fiber - Rose
HDFP-LCD16YC-B	Infinium M4 HDFP Adapter Panel, 8 Keyed Front Non-Keyed Rear LC Duplex Adapters, 16 Fiber - White
HDFP-LCD16YC-C	Infinium M4 HDFP Adapter Panel, 8 Keyed Front Non-Keyed Rear LC Duplex Adapters, 16 Fiber - Yellow
HDFP-LCD16YC-D	Infinium M4 HDFP Adapter Panel, 8 Keyed Front Non-Keyed Rear LC Duplex Adapters, 16 Fiber - Red
HDFP-LCD16YC-E	Infinium M4 HDFP Adapter Panel, 8 Keyed Front Non-Keyed Rear LC Duplex Adapters, 16 Fiber - Orange
HDFP-LCD16YC-F	Infinium M4 HDFP Adapter Panel, 8 Keyed Front Non-Keyed Rear LC Duplex Adapters, 16 Fiber - Violet
HDFP-LCD16YC-G	Infinium M4 HDFP Adapter Panel, 8 Keyed Front Non-Keyed Rear LC Duplex Adapters, 16 Fiber - Gray
HDFP-LCD16YC-H	Infinium M4 HDFP Adapter Panel, 8 Keyed Front Non-Keyed Rear LC Duplex Adapters, 16 Fiber - Blue
HDFP-LCD16YC-J	Infinium M4 HDFP Adapter Panel, 8 Keyed Front Non-Keyed Rear LC Duplex Adapters, 16 Fiber - Brown
HDFP-LCD16YC-K	Infinium M4 HDFP Adapter Panel, 8 Keyed Front Non-Keyed Rear LC Duplex Adapters, 16 Fiber - Aqua
HDFP-LCD16YC-L	Infinium M4 HDFP Adapter Panel, 8 Keyed Front Non-Keyed Rear LC Duplex Adapters, 16 Fiber - Magenta
HDFP-LCD16YC-M	Infinium M4 HDFP Adapter Panel, 8 Keyed Front Non-Keyed Rear LC Duplex Adapters, 16 Fiber - Green
HDFP-LCD16YC-U	Infinium M4 HDFP Adapter Panel, 8 Universal Keyed Front Non Keyed Rear LC Duplex Adapters, 16 Fiber- Black

DATA SHEET

Infinium M4 HDFP Adapter Panel, 8 Keyed Front Non Keyed Rear LC Duplex Adapters, 16 Fiber

General Information

- Color:
  - HDFP-LCD16YC-A (Rose)
  - HDFP-LCD16YC-B (White)
  - HDFP-LCD16YC-C (Yellow)
  - HDFP-LCD16YC-D (Red)
  - HDFP-LCD16YC-E (Orange)
  - HDFP-LCD16YC-F (Violet)
  - HDFP-LCD16YC-G (Gray)
  - HDFP-LCD16YC-H (Blue)
  - HDFP-LCD16YC-J (Brown)
  - HDFP-LCD16YC-K (Aqua)
  - HDFP-LCD16YC-L (Magenta)
  - HDFP-LCD16YC-M (Green)
  - HDFP-LCD16YC-U (Black)
- Installation: Infinium Fiber Enclosure
- Typical Application: N/A
- Connection Type: Keyed Front Non Keyed Rear LC
- Number of Ports: 8
- Type: Keyed Front Non-Keyed Rear Fiber Module
- Dust Covers: Yes

Listing Agencies/Third Party Certifications

- RoHS: Yes

Technical Information

- Connection Method: N/A
- Fiber Capacity: 16
- Polish: N/A
- Ceramic Alignment Sleeves: Yes
- TIA/EIA 604-10 Compliant: Yes
- TIA 455-21 Compliant: 500 mating cycles

Dimensions

- Depth (Metric): 29.21 mm
- Depth (US): 1.15 in
- Height (Metric): 31.49mm
- Height (US): 1.24 in
- Width (Metric): 106.42 mm
- Width (US): 4.19 in



Legrand, North and Central America

60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

© 2020 Legrand All Rights Reserved rev.07/20 15711 Keyed LC_ HDFPLCD16ZCXC