PW Steel Ladder Cable Tray
Horizontal Fitting

R H REDUCER
Horizontal Right Hand Reducer





HORIZONTAL REDUCER CATALOG NUMBERING EXAMPLE

FITTING SYSTEM NO. PRODUCT NO.

BOTTOM TYPE ← LD - 4G2I - 0818 - 12 → WIDTH

MATERIAL

BOTTOM TYPE	SIDE RAIL HEIGHT		FITTING SERIES	FLANGE DIRECTION	WIDTH
VENTED		G			06 - 6"
LD - Ladder					09 - 9"
VC! - Vented Corrugated	SIDE RAIL	G	FITTING	FLANGE	12 - 12"
NON-VENTED	HEIGHT	L	SERIES	DIRECTION	18 - 18"
SC! - Solid Corrugated	4 - 4"	T	1 – SERIES 1	I - Flange In	24 - 24"
SF! - Solid Flat Bottom	5 - 5"		2 – SERIES 2	O - Flange Out	30 - 30"
! Available for flange in only	6 - 6"				36 - 36"
VC/SC Available in steel only	7 - 7"				
SF Available in stainless steel only					

MATERIAL: STEEL/STAINLESS STEEL
FINISH SUFFIX:
G: HOT DIP GALVANIZED STEEL PER ASTM A123
L: 304 STAINLESS STEEL PER ASTM A-240
T: 316 STAINLESS STEEL PER ASTM A-240
BOTTOM: LD - LADDER
VC - VENTED CORRUGATED
SC - SOLID CORRUGATED
SF - SOLID FLAT BOTTOM
Construction: Welded
Tray Design: Tray constructed and markings are per the latest addition of NEMA Standards Publication VE1, CSA C22.2 No. 126
Connectors: All fittings are supplied with necessary connectors and fasteners
Fitting Heights (H): 4", 5", 6", 7"
Fitting Length: L=12" for Series 1 fittings
L=18" for Series 2 fittings

MAIN WIDTH (IN.) W1	BRANCH WIDTH (IN.) W2	RIGHT HAND
9	6	0809
12	6	0812
	9	0812
18	6	0818
	9	0818
	12	0818
24	6	0824
	9	0824
	12	0824
	18	0824
30	6	0830
	9	0830
	12	0830
	18	0830
	24	0830
36	6	0836
	9	0836
	12	0836
	18	0836
	24	0836
	30	0836

"Copyright LNA, Inc. Drawings are proprietary and may not be copied or otherwise duplicated or used without express written permission."

CABCS1516

Legrand
8319 State Rt. 4
Mascoutah, IL 62258 USA
800-658-4641
618-566-3250
Fax618-566-4978
www.legrand.us/cablofil