ORTRONICS

STANDARD RACK VERTICAL MANAGER

(SRVM)

#LegrandImprovingLives

legrand®

Where Simplicity Meets Versatility

Simple, Rugged, and Reliable Cable Management

SRVM SUMMARY

The Legrand Standard Rack Vertical Manager (SRVM) continues the proven success of the Mighty Mo® family, delivering simplified installation, rugged construction, and exceptional versatility. It efficiently directs, protects, and supports cables, manages slack, and provides convenient PDU mounting.

The SRVM is engineered with quick one-person installation in mind, with a lightweight design that is freestanding on the floor, and speed-bolts for faster single-tool installation. Designed to easily separate cables between RU increments in open-frame racks, the SRVM provides multiple options to route and secure cables. As networks evolve and expand, the SRVM accommodates adds and drops in a well-organized manner, ensuring optimum performance and maintaining signal integrity. Field-proven components and the renowned Mighty Mo flexible plastic fingers make the SRVM stand out among all standard vertical managers available on the market.

BENEFITS INCLUDE:

- Lightweight: Engineered to provide robust support, while minimizing overall weight for easy one-person installation.
- Dual Swing Doors: Doors open from either side, or can be removed completely with simple, dual-pin design.
- Simple Installation: Designed for one-person setup and mounting. The speed-bolt enables extremely fast single-tool installation.
- Better Cable Management: Patented cable management fingers offer generous flex to insert cables easily, while providing complete cable support.
- Segment Media: Bend limiting/cable retention clips allow network installers to separate copper and fiber within the same vertical manager.
- Accessory-Ready: Body includes PDU mounting holes (single-sided only), knockouts for cable egress, and quarter-turn accessory compatibility.

Estimated Cable Fill Capacities at 50%

SRVM: SINGLE SIDED

			# of Cables per Cable Diameter (in.)				
			0.15"	0.2"	0.25"	0.3"	.35"
Manager Width	**Part Number**	**(Usable) Area 100% (sqin.)**	0.023	0.040	0.063	0.090	0.123
4"	SRVMS704D-B	25	543	313	198	139	102
6"	SRVMS706D-B	45	978	563	357	250	183
8"	SRVMS708D-B	65	1413	813	516	361	264
10"	SRVMS710D-B	85	1848	1063	675	472	346
12"	SRVMS712D-B	105	2283	1313	833	583	427

SRVM: DOUBLE SIDED

			# of Cables per Cable Diameter (in.)				
			0.15"	0.2"	0.25"	0.3"	.35"
Manager Width	**Part Numbers**	**(Usable) Area 100% (sqin.)**	0.023	0.040	0.063	0.090	0.123
4"	SRVMD704DD-B, SRVMD704DL-B	42.5	924	531	337	236	173
6"	SRVMD706DD-B, SRVMD706DL-B	76.5	1663	956	607	425	311
8"	SRVMD708DD-B, SRVMD708DL-B	110.5	2402	1381	877	614	449
10"	SRVMD710DD-B, SRVMD710DL-B	144.5	3141	1806	1147	803	587
12"	SRVMD712DD-B, SRVMD712DL-B	178.5	3880	2231	1417	992	726

Dual with Doors



Dual Door + Latch

Single Door

Single-Sided Vertical Managers



Pin mounting design allows the door to be opened from either side, or easily taken off completely in one motion

28 Quarter turn accessory mounting holes

Note: 4 in. model has 5 and a different configuration

Speed Bolt for one-person, single-tool mounting

Note: Bolt shown larger for detail

4 knockouts for cable egress

(grommet sold separately (FCGK4-M)

12 Keyholes for PDU mounting

(Only accessible in single-sided models)



SINGLE-SIDED VERTICAL MANAGERS

Type	Configuration	Height	Width	Part Number
Single Sided	Door	7'	4"	SRVMS704D-B
			6"	SRVMS706D-B
			8"	SRVMS708D-B
			10"	SRVMS710D-B
			*12"	*SRVMS712D-B

* Note: Special Order - Lead time & minimum order quantities may apply, please contact sales support for details.



Dual-Sided Vertical Managers



DUAL-SIDED VERTICAL MANAGERS

Type	Configuration	Height	Width	Part Number
Double Sided	Door-Door	7'	4"	SRVMD704DD-B
			6"	SRVMD706DD-B
			8"	SRVMD708DD-B
			10"	SRVMD710DD-B
			*12"	*SRVMD712DD-B
	Door-Latch	7'	4"	SRVMD704DL-B
			6"	SRVMD706DL-B
			8"	SRVMD708DL-B
			10"	SRVMD710DL-B
			*12"	*SRVMD712DL-B

* Note: Special Order - Lead time & minimum order quantities may apply, please contact sales support for details.

ADDITIONAL SRVM ACCESSORIES

Part Number	Description
SRVMSPOOL-M	1/4 turn, 1/2 Spool, 4 Pack, Magnesium
MM20CMR3-B	Cable Management Ring 1.72 in x 3 in W, 14 Pack, Black
MM20CMR6-B	Cable Management Ring 1.72 in x 6 in W, 14 Pack, Black
FCGK4-M	Grommet Kit, 4", Magnesium
MM20BLC-B	Bend Limiting Clip 6.25 in L, 12 Pack - Black
SRVMLATCH4-M	Latch, 4", 10 Pack, Magnesium
SRVMLATCH6-M	Latch, 6", 10 Pack, Magnesium
SRVMLATCH8-M	Latch, 8", 10 Pack, Magnesium
SRVMLATCH10-M	Latch, 10", 10 Pack, Magnesium
SRVMLATCH12-M	Latch, 12", 10 Pack, Magnesium
SRVMUBOLT	U-Bolt Assembly, 6 Pack

SRVMSPOOL-M

SRVMLATCH8-M

SRVMUBOLT

To learn more visit

legrand.us

©2025 Legrand. All rights reserved. The industry-leading brands of Approved Networks, Ortronics, Raritan, Server Technology, and Starline empower Legrand's Data, Power & Control to produce innovative solutions for data centers, building networks, and facility infrastructures. Our division designs, manufactures, and markets world-class products for a more productive and sustainable future. The exceptional reliability of our technologies results from decades of proven performance and a dedication to research and development. V2292

Data Infrastructure
800.934.5432
legrand.us

legrand®