PASS & SEYMOUR®

Hospital Grade Devices Extra Heavy-Duty Receptacles
15 & 20A, 125V; 20A, 250V

8200I

8200ILI

Ready for the harshest medical facility environments.

8200, 8300, 8800, 8200IL, 8300IL

When it comes to toughness, this no-compromise receptacle has it all: impact-resistant nylon face and body, heavy-gauge brass strap locked into both the nd one-piece, triple-wipe, nickel-plated brass contacts. It also features screw-pressure- plate back wiring on all terminals (including the ground) for the fastest installation. Circuit label on the face and LED lamps on illuminated face models add value.

Features & Benefits

Auto-ground eliminates the necessity to terminate grounding conductor to device.

.040 inch thick, nickel-plated brass, triple-wipe power contacts for reliable plug retention.

Exclusive patented feature, circuit label on face of device allows permanent and positive circuit identification.

Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.

Extra heavy-duty brass, one-piece mounting strap with integral ground for superior structural integrity and long-term performance.



8200I

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

External nickel-plated screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

3rd Party Compliance

UL Listed, File Number E140596, Standard UL498.
Federal Specification WC596, Hospital Grade.
CSA Certified, File Number LR16063, Standard CSA-C22.2 No. 42.

Technical Information

Performance	
Electrical	
Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	250V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current
Mechanical	
Terminal Identification	Terminal Identification in accordance with UL 498 (Brass, White, Green)
Terminal Accommodation	#14 AWG - #10 AWG copper conductor only.
Product Identification	Ratings are permanent part of the device
Environmental	
Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact
Material Specs	
Face:	Nylon
Back Body:	Nylon
Line Contacts:	.040 688 Nickel-Plated Brass
Mounting Strap:	.050 688 Brass
Ground Contacts:	Strap with Integral Ground
Pressure Plate:	.031 260 Nickel-Plated Brass
Terminal Screws:	#10 Tri-Drive Brass (Neutral = Nickel-Plated Steel)
Ground Screw:	#10 Hex Tri-Drive Brass
Assembly Drive Screw:	Zinc-Plated Steel
Auto-Ground Clip:	Brass
Mounting Screws:	Tri-Drive Steel
*Illuminating Lamp	Neon

*For LED Illuminated Face Receptacles.

Warranty: 1 year



Dimensions for 15 & 20 Amp 8200I

Ordering Information

Catalog Number	Rating A.	Rating V.	Color	NEMA Config. No.
Hospital Grade Duplex Receptacles Back & Side Wire				
8200I	15	125	Ivory	5-15R
8200W	15	125	White	5-15R
8200	15	125	Brown	5-15R
8200GRY	15	125	Gray	5-15R
8200BK	15	125	Black	5-15R
8200RED	15	125	Red	5-15R
8200LA	15	125	Light Almond	5-15R
8200GN	15	125	Green	5-15R
8300I	20	125	Ivory	5-20R
8300W	20	125	White	5-20R
8300	20	125	Brown	5-20R
8300GRY	20	125	Gray	5-20R
8300BK	20	125	Black	5-20R
8300RED	20	125	Red	5-20R
8300LA	20	125	Light Almond	5-20R
8300GN	20	125	Green	5-20R
8800I	20	250	Ivory	6-20R
8800W	20	250	White	6-20R
8800	20	250	Brown	6-20R
8800GRY	20	250	Gray	6-20R
8800BK	20	250	Black	6-20R
8800RED	20	250	Red	6-20R
Hospital Grade LED Illuminated Face Duplex Receptacles Back & Side Wire				
8200ILI	15	125	Ivory	5-15R
8200ILRED	15	125	Red	5-15R
8300ILI	20	125	Brown	5-20R
8300ILRED	20	125	Red	5-20R
8300ILLA	20	125	Light Almond	5-20R

NEMA 5-15R

NEMA 5-20R

NEMA 6-20R

For more information on these and other P&S products refer to our Catalog or visit our website.

Field Uses/Vertical Markets

- **Health Care**
- **Education**
- **Insitutional**

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1-877-295-3472
www.legrand.us

Canada
1-844-977-3783
www.legrand.ca

FOLLOW US

© Copyright 2025 Legrand All Rights Reserved