WIREMOLD®

Outdoor Power Pedestal

Outdoor Power Pedestals offer new versatility to outdoor power applications

Provide Higher Power to Outdoor Locations

Designed to be used for high amperage outdoor applications, the Outdoor Power Pedestal can accommodate 15 to 60 amp devices. The pedestal is a durable solution to providing facility power to outdoor environments and applications such as food trucks, events or maintenance equipment. There are several configurations depending on the application requirements, including 1-gang, 2-gang or pin & sleeve device plates. Select configurations also include a hinged in-use cover that can be locked to prevent unauthorized access.

Outdoor Power Pedestal Features & Benefits

- **Provides standard power for facilities:** Can accommodate up to (2) 15-20A weather-resistant devices that can be used with the integrated while-in-use cover or any 3rd party while-in-use cover available for a 1 or 2 gang opening.
- **Provides higher amp power for facilities:** Pedestals can also accommodate higher 30-60A NEMA and CS devices. Higher amp devices that are watertight can be mounted directly to the pedestal while all others must use an appropriate weatherproof cover.
- **Hinged cover with locking tab:** Cover closes automatically to meet while-in-use requirements for 15 and 20 amp devices and provides capability to lock cover when not in use to prevent unauthorized access.
- **Outdoor-rated construction:** Sheet metal form designed for durability in outdoor locations. UL listed to NEMA 3R requirements to ensure optimal performance.
- **Durable, premium finishes:** Available in two outdoor-rated finishes to complement your space design. Choose from black or silver to perfectly match your project.
- **UL Listed:** Standard 1773.
- **Installation Flexibility:** Surface mount or direct bury options available to meet your design needs
- **ADA-Compliant Design*:** Engineered to meet ADA accessibility requirements, ensuring safe and convenient access to power.

*ADA compliance applies to pedestals 18" and taller

Surface-Mount Exclusives

- **Pin and Sleeve Devices:** Standard Pin and Sleeve plate supports 30A Pass & Seymour Pin and Sleeve devices. **Note:** Pin and Sleeve devices do not have standard mounting hole locations, custom plates may be needed for other brands and/or amperages.
- **Height Options of 16" or 30":** Choose from two different height options to best meet the needs of your application.
- **1 & 2 Gang Options:** Available in single or dual gang options with select configurations of dual gang including an internal divider for power and low voltage applications.

Direct Bury Exclusive

- **Prewired & Unwired Options:** Choose prewired for quick installation or unwired for full on-site customization

Compliance

CULus Listed, File Number E479489, Guide PUPR
Outdoor Power Pedestals are UL Listed to meet NEMA 3R requirements for use in outdoor locations.
Outdoor Power Pedestals comply with ADA guidelines.

Outdoor Power Pedestal Ordering Information

Catalog No./Item	Description / Specifications
XPP1G30-BK **XPP1G30-SV** **XPP1G30-BR** **XPP1G30-GN** **XPP1G16-BK** **XPP1G16-SV** **XPP1G16-BR** **XPP1G16-GN**	**Outdoor Power Pedestal, 1-Gang Device Plate –** Designed for outdoor environments with a sheet metal form ensuring optimal performance and UL listed to NEMA 3R requirements. Single gang device plate allows for mounting of devices. For 15-20A devices, weather-resistance devices must be used with an in-use cover. Devices that are 30-60A must be water-tight or fitted with a suitable weatherproof cover. Available in standard 30" (XPP1G30) or 16" (XPP1G16) heights. Consult manufacturer for custom heights. **Country of Origin: USA** **Suggested Pass & Seymour While-In-Use Covers** WIUC10SX - Standard Depth WIUCAST1 - Cast Cover WIUC10FRED - Extra Heavy Duty **Suggested Pass & Seymour Weatherproof Covers** CA8-XX: Duplex Cover CA26-XX: Decora Cover CA721-X: 1.625" CA725-X: 1.750" CA723-X: 2.125" WPG1: Flip lid 15A Turn lock WPG2: Flip Lid 20/30A Turn lock 7425: Flip Lid 20/30A Turn lock 7770: Flip Lid 50A Turn Lock



XPP1G16 (16"H)



XPP1G130 (30"H)

Catalog No./Item	Description / Specifications
XPP1G30C-BK **XPP1G30C-SV** **XPP1G30C-GN** **XPP1G30C-BR** **XPP1G16C-BK** **XPP1G16C-SV** **XPP1G16C-GN** **XPP1G16C-BR**	**Outdoor Power Pedestal, 1-Gang Device Plate with Hinged Cover –** Designed for outdoor environments with a sheet metal form ensuring optimal performance and UL listed to NEMA 3R requirements. Single gang device plate allows for mounting of devices. For 15-20A devices, weather-resistance devices must be used (included cover provides in-use protection). Devices that are 30-60A must be water-tight or fitted with a suitable weatherproof cover. The hinged cover also provides improved security with the ability to lock pedestal while not in-use. Available in standard 30" (XPP1G30C) or 16" (XPP1G16C) heights. Consult manufacturer for custom heights. **Country of Origin: USA** **Note:** Some water-tight weatherproof covers such as flip lid styles (Pass and Seymour 7770, WPG1, WPG2) for 30-60A devices may fit under the provided hood. Hood is for aesthetics only when used with 30-60A devices. **All above available in black (BK), silver (SV), green (GN) and brown (BR) finishes.**



XPP1G16C (16"H)



XPP1G30C (30"H)

Outdoor Power Pedestal Ordering Information

Catalog No./Item	Description / Specifications
XPP2G30-BK **XPP2G30-SV** **XPP2G30-BR** **XPP2G30-GN** **XPP2G16-BK** **XPP2G16-SV** **XPP2G16-BR** **XPP2G16-GN**	**Outdoor Power Pedestal, 2-Gang Device Plate –** Designed for outdoor environments with a sheet metal form ensuring optimal performance and UL listed to NEMA 3R requirements. Dual gang device plate allows for mounting of multiple devices. For 15-20A devices, weather-resistance devices must be used with an in-use cover. Devices that are 30-60A must be water-tight or fitted with a suitable weatherproof cover. Available in standard 30" (XPP2G30) or 16" (XPP2G16) heights. Consult manufacturer for custom heights. **Country of Origin: USA** **Suggested Pass & Seymour While-In-Use Covers** WIUC20X WIUCAST2 WIUC20FRED **Suggested Pass & Seymour Weatherproof Covers** CA82-X: (2) Duplex CA262-G: (2) Decora CA72-G: (2) Simplex 3796: 2.156" dia opening



XPP2G16 (16"H)



XXPP2G30 (30"H)

Catalog No./Item	Description / Specifications
XPP2G30D-BK **XPP2G30D-SV** **XPP2G30D-BR** **XPP2G30D-GN** **XPP2G16D-BK** **XPP2G16D-SV** **XPP2G16D-BR** **XPP2G16D-GN**	**Outdoor Power Pedestal, 2-Gang Device Plate with Internal Divider –** Designed for outdoor environments with a sheet metal form ensuring optimal performance and UL listed to NEMA 3R requirements. Dual gang device plate and internal divider allows for mounting of standard and low voltage devices. For 15-20A devices, weather-resistance devices must be used with an in-use cover. Devices that are 30-60A must be water-tight or fitted with a suitable weatherproof cover. Available in standard 30" (XPP2G30D) or 16" (XPP2G16D) heights. Consult manufacturer for custom heights. **Country of Origin: USA** **Suggested Pass & Seymour While-In-Use Covers** WIUC20X WIUCAST2 WIUC20FRED **Suggested Pass & Seymour Weatherproof Covers** CA82-X: (2) Duplex CA262-G: (2) Decora CA72-G: (2) Simplex 3796: 2.156" dia. opening **All above available in black (BK), silver (SV), green (GN) and brown (BR) finishes.**



XPP2G16D (16"H)



XPP2G30D (30"H)

Outdoor Power Pedestal Ordering Information

Catalog No./Item	Description / Specifications
XPP2G30C-BK **XPP2G30C-SV** **XPP2G30C-BR** **XPP2G30C-GN** **XPP2G16C-BK** **XPP2G16C-SV** **XPP2G16C-BR** **XPP2G15C-GN**	**Outdoor Power Pedestal, 2-Gang Device Plate with Hinged Cover –** Designed for outdoor environments with a sheet metal form ensuring optimal performance and UL listed to NEMA 3R requirements. Dual gang device plate allows for mounting of multiple devices. For 15-20A devices, weather-resistance devices must be used (included cover provides in-use protection). Devices that are 30-60A must be water-tight or fitted with a suitable weatherproof cover. The hinged cover also provides improved security with the ability to lock pedestal while not in-use. Available in standard 30" (XPP2G30C) or 16" (XPP2G16C) heights. Consult manufacturer for custom heights. **Country of Origin: USA**



XPP2G16C (16"H)



XPP2G30C (30"H)

Catalog No./Item	Description / Specifications
XPP2G30CD-BK **XPP2G30CD-SV** **XPP2G30CD-BR** **XPP2G30CD-GN** **XPP2G16CD-BK** **XPP2G16CD-SV** **XPP2G16CD-BR** **XPP2G16CD-GN**	**Outdoor Power Pedestal, 2-Gang Device Plate with Hinged Cover and Internal Divider –** Designed for outdoor environments with a sheet metal form ensuring optimal performance and UL listed to NEMA 3R requirements. Dual gang device plate and internal divider allows for mounting of standard and low voltage devices. For 15-20A devices, weather-resistance devices must be used (included cover provides in-use protection). Devices that are 30-60A must be water-tight or fitted with a suitable weatherproof cover. The hinged cover also provides improved security with the ability to lock pedestal while not in-use. Available in standard 30" (XPP2G30CD) or 16" (XPP2G16CD) heights. Consult manufacturer for custom heights. **Country of Origin: USA**



XPP2G16CD (16"H)



XPP2G30CD (30"H)

All above available in black (BK), silver (SV), green (GN) and brown (BR) finishes.

Outdoor Power Pedestal Ordering Information

Catalog No./Item	Description / Specifications
XPPPS30-BK **XPPPS30-SV** **XPPPS30-BR** **XPPPS30-GN** **XPPPS16-BK** **XPPPS16-SV** **XPPPS16-BR** **XPPPS16-GN**	**Outdoor Power Pedestal, Pin & Sleeve Device Plate –** Designed for outdoor environments with a sheet metal form ensuring optimal performance and UL listed to NEMA 3R requirements. The pin and sleeve device plate is for use with Pass & Seymour 30A Pin and Sleeve devices. Available in standard 30" (XPPPS30) or 16" (XPPPS16) heights. Consult manufacturer for custom heights. **Country of Origin: USA** **All above available in black (BK), silver (SV), green (GN) and brown (BR) finishes.**



XPPPS16 (16"H)



XPPPS30 (30"H)



Available Pass & Seymour Pin and Sleeve Devices

3 Wire	4 Wire	5 Wire
S330R4W	PS430R12W	PS530R9W
S330R6W	PS430R9W	PS530R7W
S330R7W	PS430R7W	PS530R5W
	PS430R5W	
	PS430R3W	

Outdoor Power Pedestal Customization Information

The outdoor power pedestal is offered at a standard height of 30″ but can be custom ordered for different heights to match your application from 16 – 48″.

For custom orders and sizes, please contact your Legrand sales representative.

Outdoor Power Pedestal Accessories Ordering Information

XPP1GP-BK
XPP1GP-SV
XPP1GP-BR
XPP1GP-GN



Replacement 1-Gang Device Plate – Replacement plate for 1-gang Outdoor Power Pedestal

Country of Origin: USA

XPP1GPL-BK
XPP1GPL-SV
XPP1GPL-BR
XPP1GPL-GN



Replacement 1-Gang, Locking Device Plate – Replacement Plate for 1-gang Outdoor Power Pedestal with Hinged Cover.

Country of Origin: USA

XPP2GP-BK
XPP2GP-SV
XPP2GP-BR
XPP2GP-GN



Replacement 2-Gang Device Plate – Replacement plate for 2-gang Outdoor Power Pedestal

Country of Origin: USA

XPP2GPL-BK
XPP2GPL-SV
XPP2GPL-BR
XPP2GPL-GN



Replacement 2-Gang Locking Device Plate – Replacement plate for 2-gang Outdoor Power Pedestal with Hinged Cover

Country of Origin: USA

XPPPSP-BK
XPPPSP-SV
XPPPSP-BR
XPPPSP-GN



Replacement Pin & Sleeve Device Plate – Replacement plate for Pin & Sleeve Power Pedestal

Country of Origin: USA

XPPC-BK
XPPC-SV
XPPC-BR
XPPC-GN



Replacement Cover for Outdoor Power Pedestal – Replacement hinged cover for Outdoor Power Pedestal

Country of Origin: USA

All above available in black (BK), silver (SV), green (GN) and brown (BR) finishes.

Outdoor Power Pedestal Accessories Ordering Information

XPP1450EV



EV Outlet Kit for Outdoor Power Pedestal – Includes NEMA 14-50 EV Weather-Rated Outlet and While-In-Use Cover to be paired with 2-Gang Outdoor Power Pedestal without internal divider: XPP2G30 and XPP2G16

Country of Origin: USA



Outdoor 100A Power Pedestal Ordering Information

Catalog No./Item		Description / Specifications
XPPPSHA16-BK **XPPPSHA16-SV** **XPPPSHA16-GN** **XPPPSHA16-BR**		**Outdoor 100A Power Pedestal, 100A Pin & Sleeve Opening** **Prewired:** Outdoor Power Pedestal, 1-Gang with Hinged Cover – Designed for outdoor environments with a sheet metal form ensuring optimal performance and UL listed to NEMA 3R requirements. Single-gang device plate comes factory-prewired with a weather-resistant 20A device, simplifying installation and ensuring reliable outdoor. **Country of Origin: USA**

Outdoor 100A Power Pedestal Customization Information

The outdoor power pedestal is offered at a standard height of 30″ but can be custom ordered for different heights to match your application from 16"–48".

For custom orders and sizes, please contact your Legrand sales representative.

Outdoor 100A Power Pedestal Accessories Ordering Information

XPPPSHAC-BK
XPPPSHAC-SV
XPPPSHAC-GN
XPPPSHAC-BR

Replacement Cover for Surface Mount Power Pedestal – Replacement hinged cover for Surface Mount Power Pedestal

Country of Origin: USA



XPPPSHAP16-BK
XPPPSHAP16-SV
XPPPSHAP16-GN
XPPPSHAP16-BR

Replacement 1-Gang, Locking Device Plate – Replacement Plate for 1-gang Outdoor Power Pedestal with Hinged Cover.

Country of Origin: USA



Direct Bury Ordering Information

Catalog No./Item	Description / Specifications
XPPDBW1G16C-BK **XPPDBW1G16C-SV** **XPPDBW1G16C-GN** **XPPDBW1G16C-BR**	**Direct Bury Power Pedestal** **Prewired:** Outdoor Power Pedestal, Direct Bury Prewired 1-Gang with Hinged Cover – Designed for outdoor environments with a sheet metal form ensuring optimal performance and UL listed to NEMA 3R requirements. Single-gang device plate comes factory-prewired with a weather-resistant 20A GFCI device, simplifying installation and ensuring reliable outdoor performance. The included cover provides in-use protection, and the hinged design offers improved security with the ability to lock the pedestal while not in use. Available in a standard 16" height (XPPDBW1G16C). Consult manufacturer for custom heights. **Country of Origin: USA** **Available in black (BK), silver (SV), green (GN) and brown (BR) finishes.**





XPPDBW1G16C

Catalog No./Item	Description / Specifications
XPPDB1G16C-BK **XPPDB1G16C-SV** **XPPDB1G16C-GN** **XPPDB1G16C-BR**	**Direct Bury Power Pedestal** **Unwired:** Outdoor Power Pedestal, Direct Bury 1-Gang with Hinged Cover – Designed for outdoor environments with a sheet metal form ensuring optimal performance and UL listed to NEMA 3R requirements. The single-gang device plate accommodates 15–20A weather-resistant devices, providing flexibility for field wiring and device selection. The included cover provides in-use protection, and the hinged design offers improved security with the ability to lock the pedestal while not in use. Available in a standard 16" height (XPPDB1G16C). Consult manufacturer for custom heights. **Country of Origin: USA** **Available in black (BK), silver (SV), green (GN) and brown (BR) finishes.**





XPPDB1G16C

Direct Bury Information

The outdoor power pedestal is offered at a standard height of 16" above grade. but can be custom ordered for different heights to match your application from 16"–30" above grade.

For custom orders and sizes, please contact your Legrand sales representative.

Direct Bury Accessories Ordering Information

XPPDBC-BK
XPPDBC-SV
XPPDBC-GN
XPPDBC-BR

Replacement Cover for Direct Bury Power Pedestal – Replacement hinged cover for Direct Bury Power Pedestal

Country of Origin: USA



XPPDB1GPL-BK
XPPDB1GPL-SV
XPPDB1GPL-GN
XPPDB1GPL-BR

Replacement 1-Gang, Locking Device Plate – Replacement Plate for 1-gang Outdoor Power Pedestal with Hinged Cover.

Country of Origin: USA



Vertical Markets

- **Commercial**
- **Entertainment**
- **Hospitality**
- **Parks**
- **Transit**

NOTE: All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1-877-295-3472
www.legrand.us

Canada
1-844-977-3783
www.legrand.ca

©2026 Legrand All Rights Reserved

FOLLOW US