MIGHTY MO 20
Dual Adjustable Base 4-Post Premium Rack

MM20 Dual Adjustable Base 4-Post Racks

provide greater flexibility and optimum efficiency in any data center or telecom room. The base angles adjust in depth with the rails reducing the overall foot print when the rail spacing is reduced. Front and rear waterfalls allow for equipment patching and server patching. All styles of Mighty Mo 20 vertical managers can be mounted to the front or rear.

Features and Benefits

- **Adjustable Depth**: Adjustable Depth: Depending on the version depth can be adjusted in 1 inch increments from 21 inches to 32 inches or 31 inches to 42 inches in depth to meet the need of nearly any application.
- **Built-in top trough with waterfalls**: Gives bend radius control and cable routing.
- **Easy Installation**: Mighty Mo 20 Racks can assemble in less than 15 minutes/rack
- **Speednuts included**: Increases speed and ease of assembly, while adding extra strength to your rack. Speednuts eliminate the need for a second wrench.
- **Vertical Cable Management Panel (Sold Separately)**: A solution for every application– Mighty Mo 20 Hex Pattern Vertical Cable Management Panel, allows for proper cable routing and bend radius control. The hex pattern accepts MM20 universal cable troughs, cable disks, and hexguard cable protectors.
- **Optimized PDU Mounting**: offering flexibility from cage, rack mount, offset rack mount mixing 1 or 2 wide and 1 or 2 deep PDU

Compatible with:

- Mighty Mo 20 Hex Pattern Vertical Cable Management Panel (Sold Separately)



Optional Mighty Mo 20 Hex Pattern Vertical Cable Management Panel

MIGHTY MO 20
Dual Adjustable Base 4-Post Premium Rack

ORDERING INFORMATION

Item Number	Rack Unit	Rail Spacing	Rail Type	Color
MM2072132DAB12-B	45	21 in - 32 in	Tapped #12-24	Black
MM2072132DAB12-W	45	21 in - 32 in	Tapped #12-24	White
MM2072132DAB38-B	45	21 in - 32 in	Punched, 3/8 in Square	Black
MM2072132DAB38-W	45	21 in - 32 in	Punched, 3/8 in Square	White
MM2073142DAB12-B	45	31 in - 42 in	Tapped #12-24	Black
MM2073142DAB12-W	45	31 in - 42 in	Tapped #12-24	White
MM2073142DAB38-B	45	31 in - 42 in	Punched, 3/8 in Square	Black
MM2073142DAB38-W	45	31 in - 42 in	Punched, 3/8 in Square	White
MM2082132DAB12-B	51	21 in - 32 in	Tapped #12-24	Black
MM2082132DAB12-W	51	21 in - 32 in	Tapped #12-24	White
MM2082132DAB38-B	51	21 in - 32 in	Punched, 3/8 in Square	Black
MM2082132DAB38-W	51	21 in - 32 in	Punched, 3/8 in Square	White
MM2083142DAB12-B	51	31 in - 42 in	Tapped #12-24	Black
MM2083142DAB12-W	51	31 in - 42 in	Tapped #12-24	White
MM2083142DAB38-B	51	31 in - 42 in	Punched, 3/8 in Square	Black
MM2083142DAB38-W	51	31 in - 42 in	Punched, 3/8 in Square	White

Optional Mighty Mo 20 Hex Pattern Vertical Cable Management Panel (Sold Separately)

Item Number	Rack Unit	Depth	Width	Color
MM207VCMP-B	45	15 in	2 in	Black
MM207VCMP-W	45	15 in	2 in	White
MM208VCMP-B	51	15 in	2 in	Black
MM208VCMP-W	51	15 in	2 in	White

TECHNICAL SPECIFICATIONS

GENERAL INFORMATION

Color	-B = Black / -W = White
Country Of Origin	USA
Type	Adjustable Premium 4-Post Rack

DIMENSIONS

Item Number	Height	Width	Rail Spacing
MM2072132DAB12-x	84.00 in	23.75 in	21.00 in - 32.00 in
MM2072132DAB38-x	84.00 in	23.75 in	21.00 in - 32.00 in
MM2073142DAB12-x	84.00 in	23.75 in	31.00 in - 42.00 in
MM2073142DAB38-x	84.00 in	23.75 in	31.00 in - 42.00 in
MM2082132DAB12-x	96.00 in	23.75 in	21.00 in - 32.00 in
MM2082132DAB38-x	96.00 in	23.75 in	21.00 in - 32.00 in
MM2083142DAB12-x	96.00 in	23.75 in	31.00 in - 42.00 in
MM2083142DAB38-x	96.00 in	23.75 in	31.00 in - 42.00 in

TECHNICAL INFORMATION

Capacity	UL 2416 Listed for 2,000 lbs. Load Rating
Compatibility	All MM20 VMD, VMS, and VML Vertical Management and Accessories