legrand®

Cablofil

FTCV090

VERTICAL 90° OUTSIDE ELBOW COVER



FEATURES

- Strong corrosion-resistant steel
- Tool-less, snap-on design
- Extended tongue support cover centers, eliminates gaps
- 18 gage steel

FITS ELBOW

FTV090

(sold separately)

	FITS TRAY HEIGHT		WIDTH		PG	BL
	INCHES	MM	INCHES	MM	STANDARD	
FTCV090 50/50	2	50	2	50	340 798	960 133
FTCV090 50/100	2	50	4	100	340 808	960 134
FTCV090 50/200	2	50	8	200	340 818	960 135
FTCV090 50/300	2	50	12	300	340 819	960 136
FTCV090 100/100	4	100	4	100	340 181	960 137
FTCV090 100/200	4	100	8	200	340 825	960 138
FTCV090 100/300	4	100	12	300	340 826	960 139
FTCV090 100/400	4	100	20	500	340 828	960 140
FTCV090 100/500	4	100	24	600	340 829	960 141

FINISHES			
SYMBOL		MATERIAL	FINISH & STANDARD
STANDARD	PG	Carbon Steel	**Pre-Galvanized:** Continuous Galvanization Before Fabrication ASTM A 653
	BL	Carbon Steel ASTM A510 Grade 1008	**Black Painted:** Black Powder Coated ASTM D 3451

© 2012 Legrand/Cablofil 02/12

Legrand/Cablofil
8319 State Route 4
Mascoutah, IL 62258 USA
1-800-658-4641
618-566-3230
Fax 618-566-3250
www.legrand.us/cablofil