AccentPLUS1 8" In-Wall Speaker.

Specifications

Speaker Components

Tweeter	Magnet: Neodymium
	Dome: 25 mm Silk
	Pivoting 30 degrees
Woofer	Magnet: 20 oz/ 100 x 45 x 15mm/Y35
	Voice Coil: 1.5" Kapton
	Cone: Etched Polypropylene
	Surround: Butyl Rubber
	Dust Cover: Polypropylene

Crossover

Tweeter	12dB / Octave
	4kHz
Woofer	N/A

Electrical

Power Rating	60 W
Impedence	8 ohm
Frequency Response	45Hz-20kHz
Efficiency	92dB 1W/1M

Mechanical

Dimensions (H x W)	14 1/8" x 10"
	358 mm x 256 mm
Cutout Dimensions	13 1/4" x 9 1/8"
	336 mm x 232 mm
Depth	3 3/8"
	86 mm

NuVo reserves the right to change specifications without notice.

Office Toll Free: 866.796.4904
Office Direct: 859.817.7200
Email: sales@nuvotechnologies.com
Web: www.nuvotechnologies.com