



Ortronics

Discontinued - Adva 0061004014 Compatible 1000Base-ZX SFP Transceiver (SMF, 1550nm, 80km, LC Duplex, DDM, I-Temp)

Part No. 0061004014-L



Adva 0061004014 Compatible 1000Base-ZX SFP Transceiver (SMF, 1550nm, 80km, LC Duplex, DDM, I-Temp)

Features & Benefits

Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.

Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

Specifications

General Info

Product Line	Ortronics	UPC Number	662875074496
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		

Dimensions

Product Width US	13.4 mm	Product Depth US	56.65 mm
Product Height US	13.4 mm		

Technical Information

Fiber Optic Cable Type	Single-Mode	Max Distance Support	80 km
Operating Temperature Min	-40 °C	Operating Temperature Max	85 °C
Connector Type	LC Duplex	Form Factor	SFP