



H3C 0231A0A7 Compatible 10GBase-LRM SFP+ Transceiver (SMF/MMF, 1310nm, 300m/220m, LC Duplex, DDM, C-Temp)



Features & Benefits

- Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.
- 99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.
- Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.
- 98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.
- Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

Specifications

General Info

Product Line	Ortronics	UPC Number	662875068204
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		

Dimensions

Product Width US	13.9 mm	Product Depth US	57.5 mm
Product Height US	13.9 mm		

Technical Information

Fiber Optic Cable Type	Single-Mode	Max Distance Support	300 m
Operating Temperature Min	0 °C	Operating Temperature Max	70 °C
Data Transfer Rate	10 Gbps	Connector Type	LC Duplex
Form Factor	SFP+		