



Arista, Calix,, Cisco, Ciena, Cyan, Extreme, Juniper, Nokia, Compatible 1000Base-CWDM SFP Transceiver

## Features & Benefits

**Guaranteed Compatible:** In System tested in over 90 OEM switches, routers and servers.

**99.98% Reliability Rate:** Functionally, optically and environmentally tested to exact specifications.

**Industry Leading Lifetime Warranty:** For more information by product line, visit our Warranty page.

**98% On-Time Delivery Rate:** Extensive inventory guarantees same day shipping.

**Full Service Technical Support:** Call, chat, email or meet for expert optical connectivity support.

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875060611
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		

### Dimensions

Product Width US	13.9 mm	Product Depth US	58.4 mm
Product Height US	8.5 mm		

### Technical Information

Fiber Optic Cable Type	Single-Mode	Max Distance Support	80 km
Operating Temperature Min	-40 °C	Operating Temperature Max	85 °C
Data Transfer Rate	1 Gbps	Connector Type	LC Duplex
Form Factor	SFP		