

Extreme 10302-BXU-60 Compatible 10GBase-BX SFP+ Transceiver (SMF, Tx: 1270nm Rx: 1330nm, 60km, LC Duplex, DDM, I-Temp)



## Features & Benefits

Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.

99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875066200
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		

### Dimensions

Product Width US	13.7 mm	Product Depth US	56.6 mm
Product Height US	12.8 mm		

### Technical Information

Fiber Optic Cable Type	Single-Mode	Max Distance Support	60 km
Operating Temperature Min	-40 °C	Operating Temperature Max	85 °C
Data Transfer Rate	10 Gbps	Connector Type	LC Duplex
Form Factor	SFP+		