

Single-Pole, Double-Throw Switch, 20A, 120/277V



## Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.	Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.
Fiber terminal insulation barriers standard.	Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.
Bodies, covers, and toggles molded of durable nylon.	Single Pole-Double Throw only.
Locking Switches supplied with one 1498-NT key.	Normally open.
For covering patents, see <a href="https://www.legrand.us/patents">https://www.legrand.us/patents</a> .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, visit <a href="http://www.legrand.us/electrical-wiring-devices/wall-plates">www.legrand.us/electrical-wiring-devices/wall-plates</a> .

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007122503
Country Of Origin	Mexico	Application Sector	Commercial, Residential
Standard	UL Listed	Type	Manual Controller

### Dimensions

Product Width US	1.5 in	Product Depth US	1.469 in
------------------	--------	------------------	----------

---

Product Height US	3.281 in
-------------------	----------

---

### Listing Agencies / 3rd Party Agencies

---

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

---

CSA File Number	17949
-----------------	-------

---

### Technical Information

---

Amperage	20 A	Number of Poles	Single Pole
----------	------	-----------------	-------------

---

Wire Size	#14 - #10 AWG
-----------	---------------

---