

Single-Pole, Double-Throw Switch, 20A, 120/277V



Features & Benefits

| | |
|---|---|
| Oversize silver alloy contacts for long life and better heat dissipation. | Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors. |
| Fiber terminal insulation barriers standard. | Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures. |
| Bodies, covers, and toggles molded of durable nylon. | Single Pole-Double Throw only. |
| Locking Switches supplied with one 1498-NT key. | Normally open. |
| For covering patents, see https://www.legrand.us/patents . | For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, visit www.legrand.us/electrical-wiring-devices/wall-plates . |

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Ivory |
| Finish | Matte | UPC Number | 785007122510 |
| Country Of Origin | Mexico | Application Sector | Commercial, Residential |
| Standard | UL listed | Type | Manual Controller |

Dimensions

| | | | |
|------------------|--------|------------------|----------|
| Product Width US | 1.5 in | Product Depth US | 1.469 in |
|------------------|--------|------------------|----------|

| | |
|-------------------|----------|
| Product Height US | 3.281 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
|------------|-----|--------------|-----|

| | |
|-----------------|-------|
| CSA File Number | 17949 |
|-----------------|-------|

Technical Information

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 20 A | Number of Poles | Single Pole |
|----------|------|-----------------|-------------|

| | |
|-----------|---------------|
| Wire Size | #14 - #10 AWG |
|-----------|---------------|
