



Pass and Seymour
15A Single Pole, Double Throw Switch, Ivory
Part No. 12501



Single-Pole, Double-Throw Switch. 15A, 120/277VAC rating. Tested to 3 Amps, 24Vdc rating.

Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Fiber terminal insulation barriers standard.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Bodies, covers, and toggles molded of durable nylon.

Single Pole-Double Throw and Double Pole-Double Throw.

Locking Switches supplied with one 1498-NT key.

Normally open.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

| | | | |
|--------------------|-------------------------|-------------|--------------|
| Product Line | Pass & Seymour | Color | Ivory |
| Finish | Matte | UPC Number | 785007125016 |
| Country Of Origin | Mexico | Switch Type | Momentary |
| Application Sector | Commercial, Residential | Standard | UL listed |
| Type | Switch | | |

Dimensions

| | | | |
|------------------|--------|------------------|----------|
| Product Width US | 1.5 in | Product Depth US | 1.469 in |
|------------------|--------|------------------|----------|

| | |
|-------------------|----------|
| Product Height US | 3.281 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
|------------|-----|--------------|-----|

| | |
|-----------------|-------|
| CSA File Number | 17949 |
|-----------------|-------|

Technical Information

| | | | |
|------------|--------------|----------|------|
| Throw Type | Double Throw | Amperage | 15 A |
|------------|--------------|----------|------|

| | | | |
|-----------------|-------------|-----------|---------------|
| Number of Poles | Single Pole | Wire Size | #14 - #10 AWG |
|-----------------|-------------|-----------|---------------|

| | | | |
|---------------|-----|---------|-----------|
| Mounting Type | Box | Voltage | 120/277 V |
|---------------|-----|---------|-----------|
