



Pass and Seymour
Locking 30A Single Pole, Double Throw Switch
Part No. 1255L



Manual Controller, Single-Pole, Double-Throw Manual Control Switch, 30A, 120/277V, Locking.

Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Fiber terminal insulation barriers standard.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Bodies, covers, and toggles molded of durable nylon.

Single Pole-Double Throw and Double Pole-Double Throw.

Locking Switches supplied with one 1498-NT key.

Normally open.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Gray |
| Finish | Matte | UPC Number | 785007410709 |
| Country Of Origin | Mexico | Application Sector | Commercial, Residential |
| Standard | UL Listed | Type | Manual Controller |

Dimensions

| | | | |
|-------------------|----------|------------------|----------|
| Product Width US | 1.5 in | Product Depth US | 1.469 in |
| Product Height US | 3.281 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
|------------|-----|--------------|-----|

| | |
|-----------------|-------|
| CSA File Number | 17949 |
|-----------------|-------|

Technical Information

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 30 A | Number of Poles | Single Pole |
|----------|------|-----------------|-------------|

| | |
|-----------|---------------|
| Wire Size | #14 - #10 AWG |
|-----------|---------------|
