



Enjoy superior safety and the convenience of built-in USB charging, in a first-of-its-kind outlet! Perfect for adding modern connectivity anywhere, including areas of the home where ground fault protection is required. Also including tamper and weather resistance, this model was designed for use on decks, patios, pool areas, and other outdoor spaces. Easily see and reset electrical trips right where they happen, while gaining two USB connections for keeping phones or tablets charged, no bulky adapter necessary.

## Features & Benefits

First outlet of its kind to add USB connection to a GFCI outlet for easier charging, anywhere

Provides reliable ground fault protection for use in outdoor spaces, including patios, decks and pool areas. Includes a trip indicator light and reset button on the outlet for easy, accessible troubleshooting

Includes traditional power outlets and two USB Type-C ports for convenient, future-proof charging. Shares 2.0A charging capacity between both ports

Self-tests every three seconds, ensuring continuous ground fault protection for greater safety. Additionally, in case of test failure, the indicator light (red LED) will flash to signal there is an issue and the outlet should be replaced

Equipped with proven SafeLock™ feature which disconnects power to the outlet if any critical components are damaged for added protection

Designed with weather-resistance for use in outdoor locations such as decks, patios and pool areas. \*Must be installed in weatherproof enclosure per NEC requirements

Protect children using a patented “invisi-shutter” system to prevent the insertion of foreign objects while maintaining a discreet, invisible effect. Meets NEC® Tamper-Resistant requirements

Installs quickly thanks to a redesigned side wire cavity for easier access. Can provide ground fault protection to downstream outlets through feed-thru wiring

## Specifications

### General Info

|                    |                         |                       |  |
|--------------------|-------------------------|-----------------------|--|
| Product Line       | Pass & Seymour          | Color                 | Gray   |
| Finish             | Matte                   | UPC Number            | 785007377934   |
| Country Of Origin  | China                   | Number of Receptacles | 2  |
| Features           | USB-C Charging          | Outlet Type           | GFCI, Self-Test, Tamper-Resistant, USB-Charging, Weather-Resistant |
| Application Sector | Commercial, Residential | Standard              | FEDSPEC  |
| Warranty Type      | 1-Year Limited Warranty | Type                  | Duplex, GFCI, Tamper-Resistant                                     |

### Listing Agencies / 3rd Party Agencies

|            |     |                     |         |
|------------|-----|---------------------|---------|
| CSA Listed | Yes | cULus ListingNumber | E140596 |
|------------|-----|---------------------|---------|

---

|              |     |                 |                                     |
|--------------|-----|-----------------|-------------------------------------|
| cULus Listed | Yes | CSA File Number | CSA C22.2 No. 223, CSA C22.2 No. 42 |
|--------------|-----|-----------------|-------------------------------------|

---

#### Additional Information

---

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

---

#### Technical Information

---

|                     |     |              |       |
|---------------------|-----|--------------|-------|
| Is Tamper-Resistant | Yes | USB Amperage | 2.1 A |
|---------------------|-----|--------------|-------|

---

|                |   |                 |   |
|----------------|---|-----------------|---|
| Number of USBs | 2 | Number of Gangs | 1 |
|----------------|---|-----------------|---|

---

|          |      |                      |     |
|----------|------|----------------------|-----|
| Amperage | 15 A | Is Weather Resistant | Yes |
|----------|------|----------------------|-----|

---

|                |         |         |        |
|----------------|---------|---------|--------|
| Indoor/Outdoor | Outdoor | Wattage | 1875 W |
|----------------|---------|---------|--------|

---

|               |     |
|---------------|-----|
| Mounting Type | Box |
|---------------|-----|

---