



Splice-On Connector SC PC OM3

## Features & Benefits

Better Insertion Loss & Return Loss Performance: Support high-bandwidth/high-speed transmission to 25G, 40G and 100G applications

Available in LC, SC and ST, Single-Mode or Multimode: Multiple connector types available

UV Cure Protection Sleeves: Strain relief boot protects the splice point

3mm Version: Brass crimp to protect splice

Factory-cleaved, pre-polished 900-micron fiber stub: Provides a quicker termination

900-micron boot conceals and protects the splice: Enables better cable management

3mm Version: 3mm boot protects splice for easy cable management

3mm Version: Tubing insert to accommodate 1.6/2.0/3.0 cordage

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875849070
Country Of Origin	China		

### Dimensions

Product Width US	2.46 in	Product Depth US	2.46 in
Product Height US	0.4 in		