Pass and Seymour

# Hospital Grade Tamper-Resistant Weather-Resistant 20A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Red

Part No. 2097HGTRWRRED



Hospital-Grade Tamper-Resistant Weather-Resistant 15A Self-Test Duplex GFCI

## Features & Benefits

| | |
|---|---|
| Hospital Grade GFCI self-test | CH versions feature a factory broken split circuit tab allowing you to control half of the receptacle. |

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | Red |
| Country Of Origin | China | Number of Receptacles | 2 |
| Outlet Type | Commercial, GFCI, Outdoor, Tamper-Resistant, Weather-Resistant | Type | Outlet |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 1.73 in | Product Depth US | 1.13 in |
| Product Height US | 4.2 in | | |

### Listing Agencies / 3rd Party Agencies

| | |
|---|---|
| cULus Listed | Yes |

### Technical Information

| | | | |
|---|---|---|---|
| Is Tamper-Resistant | Yes | Amperage | 20 A |
| Number of Poles | Double Pole | Indoor/Outdoor | Outdoor |
| Voltage | 125 V | | |