

4-way, Back and Side-Wire, Decorator Switch, 20A, 120/277V.



## Features & Benefits

Impact-resistant polycarb back body and frame.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Integral auto-ground clip for positive ground to metal boxes.

All terminal screws backed out, ready-to-install.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Tri-drive ground, terminal, and mounting screws.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007539615
Country Of Origin	Mexico	Features	Decorator Style
Switch Type	Paddle	Application Sector	Commercial, Residential
Standard	UL 20	Type	Decorator, Switch

### Listing Agencies / 3rd Party Agencies

---

CSA Listed	Yes	cULus ListingNumber	140597
------------	-----	---------------------	--------

---

cULus Listed	Yes	CSA File Number	17446
--------------	-----	-----------------	-------

---

#### Technical Information

---

Operating Temperature Min	-4 °F	Contact Rating	20amp, 120/277vac
---------------------------	-------	----------------	-------------------

---

Operating Temperature Max	140 °F	Amperage	20 A
---------------------------	--------	----------	------

---

Number of Poles	4-Way	Wire Size	#14 - #10 AWG
-----------------	-------	-----------	---------------

---

Indoor/Outdoor	Indoor	Mounting Type	Box
----------------	--------	---------------	-----

---

Operating Temperature	-20°-60°C, -4°-140°F	Voltage	120/277 V
-----------------------	----------------------	---------	-----------

---