



Heavy-Duty Decorator Hospital Grade Duplex Receptacle Back and Side Wire 15A 125V

## Features & Benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body. **Rated 15 amperes**
- Heavy-duty compact design for easier installation and long lasting performance. **Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.**
- Impact-resistant nylon face. **Terminal compartments isolated from each other for positive conductor containment.**
- All devices fit standard #26 opening wall plate. **Tri-drive terminal and mounting screws.**
- Auto-ground clip assures positive ground. **Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact**

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007784794	Country Of Origin	Mexico
Number of Receptacles	2	Application Sector	Commercial, Hospital Grade
Standard	UL498, cUL CSA, FEDSPEC	Type	Outlet

### Dimensions

Product Width US	1.322 in	Product Depth US	0.833 in
------------------	----------	------------------	----------

---

Product Height US	2.635 in
-------------------	----------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

### Technical Information

---

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
---------------------	--------------------------	------------	--------------------

---

Number of Wires	3	Temperature Rating	-40° - 60° C
-----------------	---	--------------------	--------------

---

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

---

Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
-----------	-------------	----------------	--------

---

Environmental Conditions	Flammability: UL94 V2
--------------------------	-----------------------

---