



3-way, Back and Side-Wire, Illuminated Decorator Switch, 20A, 120 volts



## Features & Benefits

Impact-resistant polycarb back body and frame.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Integral auto-ground clip for positive ground to metal boxes.

Tri-drive ground, terminal, and mounting screws.

All terminal screws backed out, ready-to-install.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007539844
Country Of Origin	Mexico	Features	Decorator Style
Switch Type	Paddle	Application Sector	Commercial, Residential
Standard	UL 20	Type	Decorator, Switch

### Listing Agencies / 3rd Party Agencies

---

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

---

CSA File Number	17446
-----------------	-------

---

#### Technical Information

---

Operating Temperature Min	-4 °F	Contact Rating	20Amp, 120Vac
---------------------------	-------	----------------	---------------

---

Operating Temperature Max	140 °F	Amperage	20 A
---------------------------	--------	----------	------

---

Number of Poles	3-Way	Wire Size	#14 - #10 AWG
-----------------	-------	-----------	---------------

---

Indoor/Outdoor	Indoor	Mounting Type	Box
----------------	--------	---------------	-----

---

Operating Temperature	-20°-60°C, -4°-140°F	Voltage	120.0 V
-----------------------	----------------------	---------	---------

---