



Locking Dust-Tight Rubber Connector, 20amp 277volt, NEMA Configuration L7-20.

## Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather

Quick lead assembly screws aid in a fast installation

Keyed body and cover for easy assembly and alignment

Two Screw cable clamp secures wire and provides superior strain relief

Industrial strength, brass blades and contacts resist heat rise while providing excellent conductivity

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007033038	Country Of Origin	United States
Standard	UL Listed, CSA Listed		

### Dimensions

Product Width US	2.14 in	Product Length US	4.06 in
------------------	---------	-------------------	---------

### Technical Information

Phase	Single	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole

---

Wire Size

14 - 10 AWG

Environmental Conditions

Moisture Resistance NEMA 4, 4X,  
12, 6, 6P/IP65, 66, 67 (Plug &  
Connector only) Flammability  
UL94V0 (boxes & wiring device  
interiors) Operating Temperature  
-40°C (without impact) to +60°C  
continuous UV resistance All  
exposed material s are UV  
stabilized

---