



Pass and Seymour
Turnlok® 27W48 Watertight NEMA 4X/6P Locking Connector
Part No. 27W48



Locking Watertight Connector, 20 amp 250 volt, NEMA Configuration L6-20, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated.

Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather

Multi-point sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated

Color coded sealing bushings provided for large range of cord diameters

Nickel-Plated blades and contacts for long lasting, superior corrosion resistance

Devices resist high-pressure hose down of 1,500 psi

Large ribs on body for a superior grip when mating

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007033779	Country Of Origin	United States
Standard	UL Listed, CSA Listed		

Dimensions

Product Width US	1.85 in	Product Length US	4.03 in
------------------	---------	-------------------	---------

Technical Information

Phase	Single	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	250.0 V

Environmental Conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65,
66, 67 (Plug & Connector only) Flammability
UL94V0 (boxes & wiring device interiors) Operating
Temperature -40°C (without impact) to +60°C
continuous UV resistance All exposed material s
are UV stabilized
