



Locking Watertight Connector, 30amp 250volt, NEMA Configuration L6-30, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated.

## Features & Benefits

Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat, and weather. Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.

Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated. Devices resist high-pressure hose down of 1,500 psi.

Color coded sealing bushings provided for large range of cord diameters. Large ribs on body for a superior grip when mating.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007033199	Country Of Origin	United States
Standard	UL Listed, CSA Listed		

### Dimensions

Product Width US	2.35 in	Product Length US	4.75 in
------------------	---------	-------------------	---------

### Technical Information

Phase	Single	Number of Wires	3
Amperage	30 A	Number of Poles	Double Pole

---

Wire Size

14 - 10 AWG

Environmental Conditions

Moisture Resistance NEMA 4,  
4X, 12, 6, 6P/IP65, 66, 67 (Plug &  
Connector only) Flammability  
UL94V0 (boxes & wiring device  
interiors) Operating  
Temperature -40°C (without  
impact) to +60°C continuous UV  
resistance All exposed material  
s are UV stabilized

---