



15A/125A Trademaster® Duplex Receptacle

Features & Benefits

Quality Materials, durability, and time-tested design

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007323283
Country Of Origin	China	Number of Receptacles	2
Outlet Type	Self-Grounding	Application Sector	Commercial, Residential
Standard	UL498, CSA C22.2 No. 42	Type	Outlet

Dimensions

Product Width US	1.32 in	Product Depth US	0.96 in
Product Height US	3.31 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile Yes

Technical Information

Temperature Rating	-30° - 60° C	Amperage	15 A
--------------------	--------------	----------	------

Number of Poles	Double Pole	Wire Size	14 - 12 AWG
-----------------	-------------	-----------	-------------

Indoor/Outdoor	Indoor
----------------	--------
