




Pass and Seymour
Trademaster® 15A 125V Self-Grounding Tamper-Resistant Duplex Receptacle, Ivory
Part No. 3232TRSI



15A/125A Trademaster® Self-Grounding, Tamper-Resistant Duplex Receptacle

Features & Benefits

Quality Materials, durability, and time-tested design

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007240283
Country Of Origin	China	Number of Receptacles	2
Outlet Type	Self-Grounding, Tamper-Resistant	Application Sector	Commercial, Residential
Standard	cULus UL498, CSA C22.2 No. 42	Type	Outlet

Dimensions

Product Width US	1.32 in	Product Depth US	1.0 in
Product Height US	3.31 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Is Tamper-Resistant	Yes	Temperature Rating	-30° - 60° C
---------------------	-----	--------------------	--------------

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	14 - 12 AWG	Indoor/Outdoor	Indoor
-----------	-------------	----------------	--------
