



Receptacle Single 30A 125/250V Turnlok®

## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007333008	Country Of Origin	Mexico
Application Sector	Industrial	Standard	Non-NEMA

### Dimensions

Product Width US	1.437 in	Product Depth US	0.97 in
Product Height US	2.25 in		

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber

140596

cULus Listed

Yes

---

Technical Information

---

Number of Wires

3

Amperage

30 A

---

Voltage

125.0 V

Environmental Conditions

Consult the Factory

---