



Two Gang Power Outlet Receptacle Opening, 2.1563 hole for 2.125 diameter device - 4 mtg. holes, Ivory, Thermoset.

## Features & Benefits

Quality materials, durability, and time-tested design.

Resistant to discoloration, grease, oil, solvent, and moisture.

Individually wrapped with color-matching screws.

Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.

## Specifications

### General Info

|                    |                         |                 |               |
|--------------------|-------------------------|-----------------|---------------|
| Product Line       | Pass & Seymour          | Color           | Ivory         |
| Finish             | Matte                   | UPC Number      | 785007386219  |
| Country Of Origin  | Mexico                  | Construction    | Plastic       |
| Wall Plate Size    | Standard Size           | Wall Plate Type | Outlet, Round |
| Application Sector | Commercial, Residential | Standard        | UL Listed     |
| Warranty Type      | 1-Year Limited Warranty | Type            | Wall Plate    |

### Dimensions

|                          |           |
|--------------------------|-----------|
| Circular Outlet Diameter | 2.1563 mm |
|--------------------------|-----------|

### Listing Agencies / 3rd Party Agencies

|            |     |                 |       |
|------------|-----|-----------------|-------|
| CSA Listed | Yes | CSA File Number | 18957 |
|------------|-----|-----------------|-------|

---

## Additional Information

---

Product Environmental Profile Yes

---

## Technical Information

---

|                |          |                 |             |
|----------------|----------|-----------------|-------------|
| Thickness      | 0.07 in  | Number of Gangs | 2           |
| Indoor/Outdoor | Indoor   | Mounting Type   | Box Mounted |
| Orientation    | Vertical |                 |             |

---