



Ortronics

Discontinued - Nokia 3HE00070CH-160 Compatible 1000Base-CWDM SFP Transceiver (SMF, 1610nm, 160km, LC Duplex, DDM, I-Temp)  
Part No. 3HE00070CH-160-L



Nokia 3HE00070CH-160 Compatible 1000Base-CWDM SFP Transceiver (SMF, 1610nm, 160km, LC Duplex, DDM, I-Temp)

## Features & Benefits

Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers. 99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875059974
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		

### Dimensions

Product Width US	13.9 mm	Product Depth US	58.4 mm
Product Height US	8.5 mm		

### Technical Information

Fiber Optic Cable Type	Single-Mode	Max Distance Support	160 km
Operating Temperature Min	-40 °C	Operating Temperature Max	85 °C
Connector Type	LC Duplex		