




Wiremold  
CableSmart 40N2 Radiused Full Capacity External Elbow Fitting  
Part No. 40N2F19WH



A 90 degree external corner with integral dividers to provide 2" (51mm) cable bend radius for UTP and fiber optic installations. Each leg is 4 1/2" (114mm). Ideal for lay-in or pull-through installations.

## Features & Benefits

A 90 degree external corner with integral dividers to provide 2" (51mm) cable bend radius for UTP and fiber optic installations. Each leg is 4 1/2" (114mm). Ideal for lay-in or pull-through installations.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776136531
--------------	----------	------------	--------------

Country Of Origin	United States	Application Sector	Commercial, Residential
-------------------	---------------	--------------------	-------------------------

Standard	cULus Listed Raceway: File E90378 Guide RJTX. Complies with Flammability requirements of UL-5A. Fittings: File E90377 Guide RJYT. Meets Article 388 of NEC. UL Listed for up to 600V. Meets Section 12-1600 of CEC.	Type	Raceway
----------	---	------	---------

### Dimensions

Product Weight US	0.75 lb	Product Depth US	2.687 in
-------------------	---------	------------------	----------

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E90377	cULus Listed	Yes
---------------------	--------	--------------	-----

### Trade Programs

---

USMCA	Yes
-------	-----

---

### Additional Information

---

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

---

### Technical Information

---

Voltage	600.0 V
---------	---------

---