



Receptacle Duplex 15A 250V Turnlok® - not designed for split circuits

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007455007
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498		

Dimensions

Product Width US	1.5 in	Product Depth US	1.15 in
Product Height US	2.27 in		

Listing Agencies / 3rd Party Agencies

CSA Listed

Yes

CSA File Number

16063

Technical Information

Number of Wires

3

Amperage

15 A

Number of Poles

Double Pole

Wire Size

18 - 10 AWG

Voltage

250.0 V
