



Heavy Cast Aluminum Cover Mounting Plate for Decorator/Ground Fault Circuit Interruptor,

Features & Benefits

Adapter, frame, and cover are heavy cast aluminum.

Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).

Neoprene gasket seals cover to frame. Moisture and dust cannot enter enclosure.

Purchase enclosure and mounting plate separately.

No. 8-32 screws hold assembly firmly in place.

Mortar keys provide positive holding means within wall.

Two keys provided for lock.

Mounts on 4 in. or 4-11/16 in. box.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Satin	UPC Number	785007179200
Country Of Origin	United States	Wall Plate Type	Custom
Application Sector	Commercial, Industrial	Standard	UL Listed
Warranty Type	1-Year Limited Warranty	Type	Weatherproof Cast Cover

Dimensions

Product Width US	6.59 in	Product Height US	7.19 in
------------------	---------	-------------------	---------

Technical Information

Indoor/Outdoor	Indoor	Mounting Type	Box Mounted
Number of Outlets	1		