

Receptacle Duplex Combination



## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007479201
Country Of Origin	United States	Application Sector	Commercial
Standard	UL 498		

### Dimensions

Product Width US	1.5 in	Product Depth US	1.199 in
Product Height US	3.28 in		

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	NO
------------	-----	-----------------	----

---

## Technical Information

---

Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	18 - 10 AWG
Voltage	125.0 V		

---