



Ten outlets. 6' (1.8m) cord. Length 48" (1.2m). 15A resettable circuit breaker. Computer grade surge protection, 15 Amps.

Features & Benefits

Ten outlets. 15' (4.6m) cord. Length 48" (1.2m). 15A resettable circuit breaker. Computer grade surge protection, 15 Amps.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776117981
Country Of Origin	Mexico	Application Sector	Commercial, Residential
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Type	PIOC

Dimensions

Product Width US	48.0 in	Product Weight US	3.46 lb
Product Height US	1.13 in	Product Length US	1.5 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Phase	Single Stage	Connection	Cord-ended
Class	75	Amperage	15 A
Short Circuit Rating	36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G]	Response Time	<1 ns
Mounting Type	Spring Clip	Mounting	Yes
Type of Indicators	Light	Voltage	600.0 V
