



Ten 20A outlets with t-slots. 6' (1.8m) cord. Length 48" (1.2m). Computer grade surge protection, 20 Amps.

Features & Benefits

Ten outlets. 15' (4.6m) cord. Length 48" (1.2m). 15A resettable circuit breaker. Computer grade surge protection, 15 Amps.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776052671
Country Of Origin	Mexico	Application Sector	Commercial, Residential
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Type	PIOC

Dimensions

Product Width US	48.0 in	Product Weight US	4.0 lb
Product Height US	1.13 in	Product Length US	1.5 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant Yes

Technical Information

Phase Single Stage Connection Cord-ended

Class 75 Amperage 20 A

Short Circuit Rating 36000 Amps [12000 Amps L-N 12000
Amps L-G 12000 Amps N-G] Response Time <1 ns

Mounting Type Spring Clip Mounting Yes

Type of Indicators Light Voltage 600.0 V
