Wiremold

# CabinetMate Plug-In Outlet Center Unit / 120V/20A/48 long/10 O/L /15' cord/Twist Lock Plug

Part No. 4810ULBD20R-TL



Ten 20A outlets with t-slots, 15' (4.6m) cord. Length 48'' (1.2m). Receptacle center-to-center 4'' (101mm). 20 Amp unit with a 20A resettable circuit breaker. Available in straight blade or Locking Plug.

## Features & Benefits

Ten 20A outlets with t-slots, 15' (4.6m) cord. Length 48'' (1.2m). Receptacle center-to-center 4'' (101mm). 20 Amp unit with a 20A resettable circuit breaker. Available in straight blade or Locking Plug.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Wiremold | UPC Number | 786776052626 |
| Country Of Origin | Mexico | Receptacle Type | Simplex |
| Number of Receptacles | 10 | Application Sector | Commercial |
| Standard | cULus Recognized: File E66421 Guide XBYS XUHT VZCA | Type | PIOC |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 1.5 in | Product Length US | 48.0 in |

### Listing Agencies / 3rd Party Agencies

| | | | |
|---|---|---|---|
| cULus ListingNumber | E66421 | cULus Listed | Yes |

### Buy American Act Compliance

| | |
|---|---|
| NAFTA | Yes |

## Additional Information

| | |
|---|---|
| RoHS Conformant | Yes |

## Technical Information

| | | | |
|---|---|---|---|
| Phase | Single | Frequency Rating | 60 Hz |
| Amperage | 20 A | Enclosure Type | Aluminum |
| Mounting Type | Spring Clip | Voltage | 125 V |
| Environmental Conditions | Dry interior locations | | |