

## Heavy-Duty Spec Grade Single Receptacle Back and Side-Wire 15A 125V



### Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Internal screw-pressure-plate back wire capable of accepting #14 - #10 AWG solid or stranded copper or copper-clad wire.

Tri-drive terminal and mounting screws.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

One-piece brass, triple-wipe power contacts for lasting retention.

Impact-resistant nylon face and thermoplastic back body.

Terminal compartments isolated from each other for positive conductor containment.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	Red
UPC Number	785007526165	Country Of Origin	Mexico
Application Sector	Commercial, Residential	Standard	UL 498, 1449, FEDSPEC

#### Dimensions

---

Product Width US	1.32 in	Product Depth US	1.093 in
------------------	---------	------------------	----------

---

Product Height US	1.68 in
-------------------	---------

---

### Listing Agencies / 3rd Party Agencies

---

cUL ListingNumber	140596	cUL Listed	Yes
-------------------	--------	------------	-----

---

### Technical Information

---

Phase	Three	Number of Wires	3
-------	-------	-----------------	---

---

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

---

Wire Size	14 - 10 AWG
-----------	-------------

---