



Wiremold
5400 Radiused Full Capacity External Elbow Fitting
Part No. 5418FO-WH



For right angle turns around external corners. Integral dividers provide 2" (51mm) cable bend radius for UTP and Fiber Optic installations. Use this elbow as a radiused alternative to 5418.

Features & Benefits

For right angle turns around external corners. Integral dividers provide 2" (51mm) cable bend radius for UTP and Fiber Optic installations. Use this elbow as a radiused alternative to 5418.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776540970
--------------	----------	------------	--------------

Country Of Origin	United States	Application Sector	Commercial, Residential
-------------------	---------------	--------------------	-------------------------

Standard	cULus Listed Raceway: File E90378 Guide RJTX. Complies with flammability requirements of UL-5A. Fittings: File E90377 Guide RJYT. Meets Article 388 of NEC. UL Listed for up to 600V. Meets Section 12-1600 of CEC.	Type	Raceway
----------	---	------	---------

Dimensions

Product Width US	5.5 in	Product Weight US	1.5 lb
------------------	--------	-------------------	--------

Product Height US	6.9 in	Product Length US	6.9 in
-------------------	--------	-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E90377	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

RoHS Compliant

Yes

Product Environmental Profile Yes

Technical Information

Voltage

600.0 V
