



Quiktron  
Q-Series 28 AWG CAT6 Patch Cable, Blue, 15 FT  
Part No. 576-RD10-015



Reduced diameter is ideal for high density data center applications. The smaller cable surface area allows for increased airflow and a smaller bend radius, which makes it easy to route through cable management panels.

## Features & Benefits

Reduced Size: 36% reduction in diameter compared to standard Cat6 cables

Standards Compliant: Meets the TIA-568-C.2 standards for patch cord performance

Snagless connector design: Prevents unwanted cable snags during installation and provides extra strain relief

Many Color Options: Available in a variety of colors

Small diameter UTP patch cord: Great for higher-density and limited applications

## Specifications

### General Info

|               |                  |                    |                        |
|---------------|------------------|--------------------|------------------------|
| Product Line  | Quiktron         | Color              | Blue                   |
| UPC Number    | 884815787185     | Country Of Origin  | Vietnam                |
| Features      | Reduced Diameter | Application Sector | Commercial, Industrial |
| Warranty Type | 5-Year           | Type               | Copper Patch Cord      |

### Dimensions

|                   |          |                   |         |
|-------------------|----------|-------------------|---------|
| Product Weight US | 0.165 lb | Product Length US | 15.0 FT |
| Cable Length      | 15 ft    |                   |         |

### Additional Information

---

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

---

## Technical Information

---

|                             |                           |                           |                |
|-----------------------------|---------------------------|---------------------------|----------------|
| Jacket Material             | PVC                       | Operating Temperature Min | -10 °C         |
| Category Performance Rating | Cat6                      | Wire Gauge                | 28 AWG         |
| Storage Humidity            | 0-90% RH (Non-Condensing) | Plating Specification     | 50 µ in Gold   |
| Jacket Application          | Riser Rated               | Bend Radius               | 0.6 in         |
| Shielded/Unshielded         | Unshielded                | Termination Style         | Pre-Terminated |
| Conductor Stranding         | Stranded                  | Operating Temperature Max | 60 °C          |
| Jacket Rating               | CM Rated                  | Cable Diameter            | 0.15 in        |
| Braid                       | Non-braided Wiring        | Operating Temperature     | -10°-60°C      |
| Operating Humidity          | 0-90% RH (Non-Condensing) | Conductor Material        | Copper         |
| Voltage                     | 300.0 V                   | Storage Temperature       | -40° - 60° C   |

---