



Pass and Seymour  
Discontinued - Short Strap Spec Grade Single Receptacle, Side Wire, 20A, 250V, White  
Part No. 5858W



Short Strap Spec Grade Single Receptacle, Side Wire, 20amp 250volt, White.

## Features & Benefits

- Auto-ground clip assures positive ground. Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength. Backed-out tri-drive steel terminal screws.
- One-piece brass triple-wipe power contacts for lasting retention. For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#). Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007585827	Country Of Origin	Mexico
Application Sector	Commercial, Residential	Standard	UL 498, WC596

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

### Technical Information

---

Phase	Three	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG		

---