



Hard Use Spec Grade Combination Duplex Receptacle Side-Wire 20A 125/250V



Features & Benefits

- Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly.
 - Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
 - 8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.
 - Tri-drive terminal and mounting screws.
 - Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
 - Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
 - Impact-resistant nylon face.
 - Terminal compartments isolated from each other for positive conductor containment.
 - Auto-ground clip assures positive ground.
 - For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007589009	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL498, FEDSPEC

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
------------------	----------	------------------	---------

Product Height US	2.635 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Side Wire
---------------------	--------------------------	------------	-----------

Number of Wires	3	Temperature Rating	-40° - 60° C
-----------------	---	--------------------	--------------

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	14 - 10 AWG	Environmental Conditions	Flammability: UL94 V2
-----------	-------------	--------------------------	-----------------------
